

# XY2CZ302

Telemecanique Emergency stop rope pull switches XY2C, red galvanised cable, Ø 3.2 mm, L 25.5 m, for XY2C



## Main

Range of Product	Telemecanique Emergency stop rope pull switches XY2C
Accessory / separate part category	Separate parts
Accessory / Separate Part Type	Galvanised cable
Product Compatibility	XY2CH XY2CJ XY2CB
Accessory / separate part destination	Rope pull switch Emergency stop rope pull switch
Cable outer diameter	0.13 in (3.2 mm)
Cable length	83.66 ft (25.5 m)

## Complementary

Net Weight	1.52 lb(US) (0.69 kg)
------------	-----------------------

## Ordering and shipping details

Category	22441 - LIMIT SWITCHES,CABLE PULL
Discount Schedule	T
GTIN	3389110590913
Nbr. of units in pkg.	1
Package weight(Lbs)	29.21 oz (828 g)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.01 in (5.1 cm)
Package 1 width	10.43 in (26.5 cm)
Package 1 Length	10.94 in (27.8 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Weight	8.07 lb(US) (3.66 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	64
Package 3 Weight	147.84 lb(US) (67.06 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------