

SHOWA
730

The pinnacle of chemical-resistance, comfort and grip, SHOWA 730 is a flock-lined, 15 mil glove designed with the full scope of performance in mind.

FEATURES

- Unsupported 100% nitrile
- Flock-lined
- 15 mil thick
- Bisque grip
- 13" length

BENEFITS

- Provides chemical resistance against a broad range of solvents, oils, animal fats and other chemicals
- Mechanical resistance
- Bisque finish grip makes wet work easier and safer
- Ergonomic design maximizes comfort

INDUSTRY



Agriculture



Automotive



Chemical



Landscaping



Municipal Services

IDEAL APPLICATIONS

- Chemical spray and treatment
- Light chemical handling in agriculture, horticulture
- Light assembly of oil-coated pieces
- Painting and spray workshops
- Coating preparation
- Washing & cleaning



TAA PRODUCTS

MATERIAL

- Cotton flock
- Unsupported

COATING

- chemical resistant
- Nitrile
- Water resistant

GRIP

- Bisque

STANDARDS



EN ISO 374-1:2016/Type A

EN ISO 374-5:2016



SHOWA
730



PACKAGING

- 12 Pair per polybag
- 12 Polybags per case
- 144 Pair per case



COLOUR

- Green



SIZES

- XS
- S
- M
- L
- XL
- XXL



THICKNESS

- 15 mil



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
747



MATERIAL
Unsupported

COATING
chemical resistant

SHOWA
731



MATERIAL
Cotton flock

COATING
Biodegradable

SHOWA
728



MATERIAL
Unsupported

COATING
Biodegradable

SHOWA
707HVO



MATERIAL
Unsupported

COATING
Biodegradable

[USER INSTRUCTIONS

Protection against mechanical risks, with electrostatic properties. Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. All clothing and shoes worn with the glove with electrostatic dissipation properties must also be designed taking the electrostatic risk into account.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved