

Construction Calculators

Compare the Features

Construction Master Pro Model 4065	Construction Master Pro Trig Model 4080	Construction Master 5 Model 4050	Measure Master Pro Model 4020
--	---	--	---

Work in and convert between all dimensional units

Feet-Inch-Fraction, Inch Fraction, Yards	✗	✗	✗	✗
Decimal Feet (10ths, 100ths), Decimal Inches	✗	✗	✗	✗
Handles All Construction Fractions	✗	✗	✗	✗
Full Metrics (m, cm, mm)	✗	✗	✗	✗
Weight per Volume Conversions	✗	✗	✗	✗

Right Angle Solutions

Complete Right Angle/Rafter Calculations	✗	✗	✗	
Pitch Key (Slope and Grade)	✗	✗	✗	
Rise, Run, Diagonal/Common Rafters	✗	✗	✗	
Hip/Valley and Jack Rafters	✗	✗	✗	
Irregular Hip/Valley and Jacks	✗	✗	✗	
Rafter Cutting Angles (Plumb, Cheek and Level Cuts)	✗	✗		
Stair Layouts (Basic and Advanced - Riser Limit, Stairwell Opening, Headroom, Floor Thickness)	✗	✗	Basic	
Rake-Walls	✗	✗	✗	
Studs: Find Number On-center	✗	✗	✗	

Area and Volume Solutions

Square and Cubic Dimensions	✗	✗	✗	✗
Roof – Bundles, Squares, 4x8 Sheets, Pitch, Plan Area	✗	✗		
Drywall, Siding and Paneling - 4x8, 4x9 and 4x12	✗			
Column/Cone Area and Volume	✗	✗		
Basic and Advanced Circular Calculations	✗	✗	Basic	Basic
Length, Width and Height Keys, Automatic Area and Volume	✗			✗
Blocks, Footings	✗			

Special Functions

Trigonometric (Sine, Cosine, Tangent, Arcsine, Arccosine, Arctangent)		✗		
Board Feet	✗	✗	✗	✗
Works as a Regular Calculator (+, -, x, ÷, +/-, %, π, 1/x, x ² , √x)	✗	✗	✗	✗
User-Definable Preferences	✗	✗	✗	✗
Entry Editing Backspace Key	✗	✗	✗	✗
Cost per Unit (Total costs based on unit price)	✗	✗	✗	✗
Equal sided Polygon	✗	✗		
Compound Miters and Spring (Crown) Angle Cuts	✗	✗		

Additional Capabilities and Characteristics

Paperless Tape	✗	✗	✗	✗
Number of Memories	4	4	4	4

Included with Calculator

Online User's Guide	✗	✗		
Pocket Reference Guides in English and Spanish	✗	✗	✗	✗
Long-Life Batteries	✗	✗	✗	✗
Full One-Year Limited Warranty	✗	✗	✗	✗