



Miniature Circuit Breaker Lockouts



Equipping your employees with the proper lockout tools and warning devices can save lives, reduce employee downtime and cut insurance costs. When seeking a safe and effective method for locking out miniature circuit breakers, Brady has lockout devices to complete the job.

▶ **New Miniature Circuit Breaker Lockout – Universal Fit**


The latest Miniature Circuit Breaker Lockout – Universal Fit is designed for ABB, Hager, Siemens breakers and more, making it your go-to lockout device for a variety of breakers. With this lockout device, you'll get a secure lockout in a low-profile design.

- Low-profile design allows for panel door closure
- Complete lockout by attaching a Brady safety padlock with shackle diameter up to 9/32"

▶ **Other Brady Miniature Circuit Breaker Lockouts**

The Miniature Circuit Breaker Lockout Devices from Brady are designed with specific circuit breakers in mind so that lockout can be completed safely and effectively without any tools. These devices feature quick and easy installation with no tools required, and colored tips to easily differentiate between devices:

- Miniature Circuit Breaker Lockout – ABB MS325 Series
- Miniature Circuit Breaker Lockout – Tie-Bar Lockout
- Miniature Circuit Breaker Lockout – Pin-Out Standard
- Miniature Circuit Breaker Lockout – Pin-In Standard
- Miniature Circuit Breaker Lockout – Pin-Out Wide



Catalog #	Description	Qty
149514	New Universal Fit (UF)	1
149515	New Universal Fit (UF)	6
149433	ABB MS325 (MS)	1
149434	ABB MS325 (MS)	6
90844	Pin-Out Standard (POS)	1
90845	Pin-Out Standard (POS)	6

Catalog #	Description	Qty
90847	Pin-In Standard (PIS)	1
90848	Pin-In Standard (PIS)	6
90850	Pin-Out Wide (POW)	1
90851	Pin-Out Wide (POW)	6
90853	Tie-Bar Lockout (TBLO)	1
90854	Tie-Bar Lockout (TBLO)	6

Miniature Circuit Breaker Compatibility Chart

Brand	Poles	Model No.	Type	Catalog # (1/pkg)
ABB	1	S222	POS, UF	90844, 149514
ABB	1	F374	POS, UF	90844, 149514
ABB	1	S251, S261, S263	POS, UF	90844, 149514
ABB	1	S272, S253	POS, UF	90844, 149514
ABB	3	S253	POS, UF	90844, 149514
ABB	3	MS325	MS, UF	149433, 149514
AEG	2	E82S	PIS	90847
Allen-Bradley	1,2,3	1492-CB1, 2, 3	POS	90844
Buschmat	1	S46	POS	90844
Clipsal	1	4CB116	POS	90844
Clipsal	3	4CB320	POS	90844
E-TA	1	911225	PIS	90847
E-TA	2	911220G	POS	90844
FAZ	4	C16	POS	90844
FAZ	1	C16	POS	90844
GE Vynckier	3	Series E	PIS	90847
GE Vynckier	3	Series G	PIS	90847
GE Vynckier	4	Series E	PIS	90847
GE Vynckier	1	Series G	PIS	90847
GE Vynckier 16A	2	Series E	PIS	90847
GE Vynckier C16, 16A	1	Series E	PIS	90847
Hager	3	453717	POS, UF	90844, 149514
Hager	2	MW216A	POS, UF	90844, 149514
Hager	4	MW620A	POS, UF	90844, 149514
Kapp	1	LS68	PIS	90844
Legrand	2	1935	TBLO	90844

Brand	Poles	Model No.	Type	Catalog # (1/pkg)
Legrand	3	1980	TBLO	90844
Legrand	4	1980	TBLO	90844
Legrand	2	4302	PIS	90847
Legrand	3	6469	PIS	90847
Legrand	1	1908	PO	90844
Merlin Gerin	3	C80A	TBLO, POW	90850, 90853
Merlin Gerin	2	B100A	TBLO, POW	90850, 90853
Merlin Gerin	1	C60N	POS	90844
Merlin Gerin	1	C32N	POS	90844
Merlin Gerin	2	C60N	POS	90844
Merlin Gerin	4	C60N	POS	90844
Merlin Gerin	3	C32N	POS	90844
Merlin Gerin	3	C45AD	POS	90844
Proteus	1	C16	POS	90844
Proteus	1	C6	POS	90844
Proteus	3	C6	POS	90844
Siemens 17U	2	5SQ12	TBLO, UF	90853, 149514
Siemens 17U	3	5SQ13	TBLO, UF	90853, 149514
Siemens 17U	4	5SQ16	TBLO, UF	90853, 149514
Siemens 17U	1	5SQ11	POW, UF	90850, 149514
Siemens C10	1	5SX1	POW, UF	90850, 149514
Siemens C32	2	5SX1-2	TBLO, UF	90853, 149514
Siemens C70	3	5SX13	TBLO, UF	90853, 149514
Siemens L20A	2	5SN2-2	TBLO, UF	90853, 149514
Sursum	3	EA53	PIS	90847
Wylex	2	WRS40/2	POS	90844

 **For more information,
visit BradyID.com/lockout**

USA
Customer Service: 1-888-272-3946
Inside Sales: 1-888-311-0775
BradyID.com

Canada
Customer Service: 1-800-263-6179
BradyCanada.ca

Mexico
Customer Service: 1-800-262-7777
Inside Sales: 1-800-262-7777 ext 177
BradyLatinAmerica.com