



PIG® Grippy® Leak & Drip Mat

#25800 - Mediumweight • 32"W x 50'L • 1 roll



Grippy® Mat is the one-of-a-kind absorbent mat that stays put no matter what™ without bunching, sliding or shifting. Patent-pending adhesive backing keeps the mat in place to absorb fluids, cushion parts, line benches and protect surfaces.

- Specially formulated, full coverage adhesive backing holds tight but leaves no residue
- Eight layers of fine-fiber polypropylene safely absorb oils, coolants, water, gasoline, solvents, auto fluids, paint overspray, battery acid and most other liquids
- Tough, spunbond top layer stands up to foot and light-wheeled traffic plus wear and tear from parts and tools
- Poly backing creates a liquid-proof barrier to stop absorbed fluids from passing through
- When used as part of your floor safety program, high-traction surfaces such as PIG® Grippy® Mat have been proven to reduce slip-and-fall claims by as much as 90%
- Tested and certified by the National Floor Safety Institute (NFSI)
- Peels up easily for quick changeouts; reduces cleanup time for a more productive shop
- Apply to any clean, dry, oil-free surface; cuts easily with scissors or utility knife



New Pig

By Phone:
1-800-HOT-HOGS® (468-4647)

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton, PA 16684-0304
©2016 New Pig Corporation. All rights reserved.
PIG and PIG Logo are trademarks in the U.S. and other countries

ITEM: 25800 - Pg 1 of 2

25800 Specifications

Dimension:	32" L x 50' W
Sold as:	1 roll
Color:	Blue
Composition:	Absorbent - Polypropylene Stitching - Polyester Adhesive Backing - Proprietary Adhesive Material
Absorbency	Up to 5.25 gal. per roll
Fluid Absorbed:	Oils, Coolants, Solvents, Water
UNSPSC:	47131901 - Absorbent mats
Configuration:	Mat Roll
Durability Level:	Heavy Foot Traffic
Industry:	Industrial Facilities; Shops & Garages
Mat Weight/Absorbency Level:	Mediumweight
Poly-Backed Barrier:	Yes
Special Feature:	Sticky Adhesive Backing
Walking Surface:	Absorbent Top
Mat Quantity/Length:	(1) 50' mat per roll

25800 Technical Information

Certifications, Approvals and Ratings

NFSI Certified, ANSI B101.1- 2009

25800 Metric Equivalent

Absorbency	Up to 19.9 L per roll
Dimensions	81.3cm W x 15m L
Weight	5.4 kg



New Pig

By Phone:
1-800-HOT-HOGS® (468-4647)

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton, PA 16684-0304
©2016 New Pig Corporation. All rights reserved.
PIG and PIG Logo are trademarks in the U.S. and other countries

ITEM: 25800 - Pg 2 of 2

352589