



SURE-FOOT Grit-Coated Step Covers

Sure-Foot Grit-Coated Step Covers provide slip resistance, durability and a permanent anti-slip solution. Fiber glass step covers are lightweight and ideal for use on structurally sound surfaces.



3" Step Cover with 1" nose (Available in Yellow or Black)



9" Step Cover with 1" nose (Available in Solid or Two Colors)



11.75" Step Cover with 2" nose (Available in Solid or Two Colors)




PROUDLY MADE IN THE UNITED STATES






Our Fiber Glass products are coated with a proprietary blend of mineral abrasive epoxy grit. Surfaces such as gratings, mezzanines, steps, inclines, ramps and floors can be covered with either fiber glass step covers or walkway panels. All are available in three distinct grit coating options: Heavy Duty, Medium and Fine as well as Yellow or Black



Heavy Duty



Medium

Specialty sizes and panels are available upon request.



PROUDLY MADE IN THE UNITED STATES





Grit-Coated Fiberglass Step Covers

Grainger Part Number	Item Description
31AP24	3" x 24" YEL Nosing HD Grit
31AP25	3" x 36" YEL Nosing HD Grit
31AP26	3" x 48" YEL Nosing HD Grit
31AP27	3" x 60" YEL Nosing HD Grit
31AP28	3" x 24" YEL Nosing MED Grit
31AP29	3" x 36" YEL Nosing MED Grit
31AP30	3" x 48" YEL Nosing MED Grit
31AP31	3" x 60" YEL Nosing MED Grit
31AP32	3" x 24" BLK Nosing HD Grit
31AP33	3" x 36" BLK Nosing HD Grit
31AP34	3" x 48" BLK Nosing HD Grit
31AP35	3" x 60" BLK Nosing HD Grit
31AP36	3" x 24" BLK Nosing MED Grit
31AP37	3" x 36" BLK Nosing MED Grit
31AP38	3" x 48" BLK Nosing MED Grit
31AP39	3" x 60" BLK Nosing MED Grit
31AP40	9" x 24" YEL/BLK Nosing HD Grit
31AP41	9" x 36" YEL/BLK Nosing HD Grit
31AP42	9" x 48" YEL/BLK Nosing HD Grit
31AP43	9" x 60" YEL/BLK Nosing HD Grit
31AP44	9" x 24" YEL/BLK Nosing MED Grit
31AP45	9" x 36" YEL/BLK Nosing MED Grit
31AP46	9" x 48" YEL/BLK Nosing MED Grit
31AP47	9" x 60" YEL/BLK Nosing MED Grit
31AP48	11.75" x 24" YEL/BLK Nosing HD Grit
31AP49	11.75" x 36" YEL/BLK Nosing HD Grit
31AP50	11.75" x 48" YEL/BLK Nosing HD Grit
31AP51	11.75" x 60" YEL/BLK Nosing HD Grit
31AP52	11.75" x 24" YEL/BLK Nosing MED Grit
31AP53	11.75" x 36" YEL/BLK Nosing MED Grit
31AP54	11.75" x 48" YEL/BLK Nosing MED Grit
31AP55	11.75" x 60" YEL/BLK Nosing MED Grit
SPECIALTY ORDERS AVAILABLE UPON REQUEST	

MAINTENANCE

Epoxy surface can be swept to loosen and remove dirt. Step covers can be cleaned using a general purpose industrial floor cleaner. For caked on dirt, use a stiff bristled brush with the industrial cleaner. Step covers can be pressure sprayed up to 1000 psi.



For more information contact your Grainger Representative or visit Grainger.com®."

8SSP6421

AVAILABLE THROUGH
GRAINGER®
||| FOR THE ONES WHO GET IT DONE