

# FINE FISSURED™ Second Look®

Scored Tegular  
medium texture

**SUSTAIN™**  
High Performance  
Sustainable Ceiling Systems  
(white only)

**GREENGUARD**  
Gold Certified  
(details below)

**Declare.**

**LEED® WELL™ LBC**


UP TO **56%** RECYCLED CONTENT

- energy management
- construction waste mgmt
- regional materials
- design for flexibility
- EPD
- recyclable/extended producer resp.

LOCATION DEPENDENT

Calculate sustainability with GreenGenie™  
armstrongceilings.com/greengenie

\$\$\$\$



▲ Fine Fissured™ Second Look® II panels with Suprafine® XL® 9/16" suspension system

Economical panels; Scored plank or geometric visual with standard acoustical performance.

### KEY SELECTION ATTRIBUTES


- Fine Fissured™ Second Look® panels are part of the Sustain® portfolio, and meet the most stringent industry sustainability compliance standards today
- Geometric scored visuals
- Economical option to create a designer look
- Mold- and mildew-resistant surface
- 10-Year replacement panel available for item 1761



### COLOR



### FACE VIEW



Second Look I



Second Look II



Second Look III

### VISUAL SELECTION

armstrongceilings.com/catdwgs	Susp. Dwg.	Item No.	Dimensions (Inches)	Visual	Look
FINE FISSURED™ Second Look®	11	1760	24 x 48 x 3/4"		Second Look I
15/16" Angled Tegular		1761	24 x 48 x 3/4"		Second Look II
		1861	24 x 48 x 3/4"		Second Look II
		1762	24 x 48 x 3/4"		Second Look III
9/16" Angled Tegular	27	1765	24 x 48 x 3/4"		Second Look I
		1766	24 x 48 x 3/4"		Second Look II

### PERFORMANCE SELECTION


Dots represent high level of performance.

UL Classified Acoustics	Total Acoustics <sup>1</sup>	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resistant	Certified Low VOC Emissions	Durability	Recycled Content	Recycle Program	Warranty
NRC + CAC =										
0.55 35	N/A	Class A	0.82	•	•	•	Std	Std	•	•
0.55 35	N/A	Class A	0.82	•	•	•	Std	Std	•	•
0.55 35	N/A	Fire Guard™	0.82	•	•	•	Std	Std	•	•
0.55 35	N/A	Class A	0.82	•	•	•	Std	Std	•	•
0.55 30	N/A	Class A	0.82	•	•	•	Std	Std	•	•
0.55 30	N/A	Class A	0.82	•	•	•	Std	Std	•	•

<sup>1</sup> Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.

### SUSPENSION SYSTEMS

NOTE: It is not recommended to install Silhouette® or Interlude® grid with Second Look® panels.



### PHYSICAL DATA

**Material**  
Wet-formed mineral fiber

**Surface Finish**  
Factory-applied latex paint

**Fire Performance**  
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).  
Fire Guard™: A fire-resistive ceiling when used in applicable UL assemblies

**ASTM E1264 Classification**  
Type III, Form 2, Pattern C E K  
Fire Class A

**Humidity/Sag Resistance**  
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications.

**Anti-Mold/Mildew**  
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

**VOC Emissions**  
**GREENGUARD Gold Certified**  
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

**Insulation Value**  
R Factor – 1.6 (BTU units)  
R Factor – 0.28 (Watts units)

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS  
UL.COM/GG  
UL 2818



**30-Year Performance Guarantee & Warranty**  
When installed with Armstrong® suspension system. Details at armstrongceilings.com/warranty

**Design Consideration**  
Do not mix Fine Fissured™ Second Look® panels with standard Fine Fissured panels in the same room. It is not recommended to install Silhouette® or Interlude® grid with Second Look® panels.

**Weight; Square Feet/Carton**  
0.75 lbs/SF; 80 SF/ctn

**Minimum Order Quantity**  
1 carton

**Metric Items Available**  
1761M - Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.

TechLine / 1 877 276-7876  
armstrongceilings.com/finefissured  
BPCS-3027-722

LEED® is a registered trademark of the U.S. Green Building Council; Declare® and Living Building Challenge® (LBC) are registered trademarks of the International Living Future Institute; WELL™ and WELL Building Standard are trademarks of the International WELL Building Institute; UL and UL Certified are trademarks of UL LLC; all other trademarks used herein are the property of AWI Licensing LLC and/or its affiliates © 2022 AWI Licensing LLC

