



# ANTI-VIBRATION AIR GLOVE®

## High Visibility Anti-Vibration Gloves Utilizing Patented Air Glove Technology

Used with multiple vibrating and pneumatic tools in low-light conditions  
Mechanic's style ensures maximum comfort, dexterity and fit

- › Synthetic ultra suede leather provides excellent wear and flexibility
- › Silicone dots on the palm and fingertips ensure outstanding grip and flexibility
- › Bright glow mesh back allows ventilation
- › Durable Bubble Glove® bladder in the palm, fingers and thumb protects from vibration
- › Full finger design offers maximum protection while maintaining flexibility and tactile feedback for finger sensitivity and tool control
- › Reflective strips on the back of the hand and fingers to enhance visibility
- › Glow in the dark wrist cuff with adjustable hook and loop closure
- › Protects from vibration when using hand-held or hand guided power tools and machines such as sanders, grinders, disc cutters, hammer drills, brush cutters and mowers

Model **BGHIVIS**



The IMPACTO Air Glove reduces vibration energy transmission to the palm and fingers. Non-permeable polymer bladder with multiple individual air chambers provides effectiveness that won't degenerate. Soft, flexible bladder is designed to conform to the flex-lines of the palm and fingers helping to maintain tool control. The multiple air chambers construction of the Air Bladder ensures long lasting wear that won't bottom out. The Air Bladder helps prevent job specific impact and vibration hazards in the workplace. Full finger Air Gloves are in conformance with International Anti-Vibration Glove Standard EN ISO 10819 Mechanical Vibration and Shock-Hand-Arm Vibration and North American Standard ANSI S2.73-2002 (R 2007) / ISO 10819.



### Meets ISO 10819:1996 & ANSI S2.73-2002 (R 2007) | ISO 10819:2013



EN 388:2016  
Protective gloves against mechanical risks  
EN 420:2003+A1:2009  
General requirements for gloves

Sizing: Measure the circumference of the hand at the base of fingers.

Washing: Hand wash in cold water and soft detergent. Do not bleach, do not dry by machine, do not dry clean.

US Patents 7,865,969, D768,336. Canadian Patent 2,496,077. Other patents pending.

Part	Glove	Hand	Circumference
BGHIVIS20	S	7	7" - 8" / 18-20 cm
BGHIVIS30	M	8	8" - 9" / 20-23 cm
BGHIVIS40	L	9	9" - 10" / 23-28 cm
BGHIVIS50	XL	10	10" - 11" / 28-33 cm
BGHIVIS60	XXL	11	11" + / 33 + cm

TRUSTED PROTECTION

ISO 9001:2015



**IMPACTO.CA**

N. America 888 232 0031

Free phone UK 0800 0280 243

T: 613 966 0062 F: 613 966 0067

PO BOX 524, BELLEVILLE, ON K8N 5B2

[impacto@impacto.ca](mailto:impacto@impacto.ca)

Distributed by,

# IMPACTO

PROTECTIVE PRODUCTS