



Illustrated Parts Breakdown




Specifications:

Model PSWSA1SK

Voltage	115VAC, $\pm 10\%$, 1 PH, 60 Hz
Size	42-1/2" H, 12" W, 12-1/2" D
Shipping Weight	52 lbs.
Cold Water Capacity	.6 GPH
Compressor	1/20 hp
Compressor (Full Load)	1.2 amps
Refrigerant	134a
Refrigerant Charge	1.375 oz.

Model PSWSA1SHS

Voltage	115VAC, $\pm 10\%$, 1 PH, 60 Hz
Size	42-1/2" H, 12" W, 12-1/2" D
Shipping Weight	58 lbs.
Cold Water Capacity	.6 GPH
Compressor	1/20 hp
Compressor (Full Load)	5.5 amps
Refrigerant	134a
Refrigerant Charge	1.375 oz.




Parts List


Item #	Description	PSWSA1K	PSWSA1SHS
1	Baffle	030914-001	030914-001
2	Cooling Tank Fitting	020485	020485
3	Cook Cooling Tank Fitting	028302-002	N/A
4	Cook Outlet Tube	028291-003	N/A
5	Gasket, Hot Water Inlet	N/A	027965-001
6	Gasket, Water Outlet Tube	027139	027139
7	Water Outlet Tube, Cold	020484-004	020484-004
8	Cooling Tank Insulation	033186-001	033186-001
9	Cooling Tank Assy	033913-003	033193-001
10	Shelf Insulation	033187-001	033188-001
11	Shelf	033185-001	033185-001
12	Cold Control	027040-022	027040-022
13	Heat Exchanger	030749-005	030749-005
14	Rear cover panel	64-0042-05	64-0042-05
15	Condenser Adapter Plate	036781-001	036781-001
16	Support Bracket	28-0001-01	28-0001-01
17	Condenser	035972-001	035972-001
18	Rocker, Hot Tank Switch	N/A	029545-004
19	Service Cord	026540-055	026540-055
20	Refrigerant Drier	034343-002	034343-002
21	Compressor Base	033191-001	033191-001
22	Compressor Assy, B25H5	036904-001	036904-001
23	Cabinet Base	64-0046-09	64-0046-09
24	Lower Front Panel	037152-002	037152-002
25	Drip Tray & Grille	64-0407-00	64-0407-00
26	Upper Front Panel	035917-001	035917-001
27	Side Panel	037153-102	037153-102
28	Cabinet Top	034706-001	034706-001
29	Faucet, Cold Whi / Blu	032135-106	032135-106
	Faucet, Cold Blk / Blk	032135-121	032135-121
30	Faucet, Cook Whi / Whi	032135-105	N/A
	Faucet, Cook Blk / Whi	032135-122	N/A
31	Faucet, Hot Whi / Red	N/A	032135-114
	Faucet, Hot Blk / Red	N/A	032135-123
32	Faucet, Gasket	033190-005	033190-005
33	Hot Tank Assy	N/A	035187-103
34	Hot Thermostat	N/A	033588-002
35	Heat Limiter	N/A	033588-003
36	Hot Tank Insulation (Body)	N/A	035911-002
37	Extension tube	N/A	035024-001
38	Drain Valve Assy	N/A	033970-003
39	Air Filter	031823-002	031823-002
40	Gasket	033354-001	033354-001
41	Mechanical Float Assy. (includes # 39 & # 40)	031164-002-SP	031164-002-SP
Parts Not Shown			
	Relay	036056-001	036056-001
	Overload for Huayi AES-25-DS Series	036055-001	036055-001
	Overload for Huayi B25H5 Series	036903-001	036903-001
	Strain Relief Clamp	018541	018541
	Handle, Plastic Cooler	034050-002	034050-002
	OASIS ID Badge	036790-001	036790-001

Wiring Diagrams:

PSWSA1K



PSWSA1SHS



OASIS International

222 East Campus View Blvd · Columbus, Ohio 43235 U.S.A.
 1-800-64-OASIS (1-800-646-2747)
www.oasiscoolers.com