



We Know Water.

ARTESIAN POU COOLER

Features:

- Stylish design fits well in contemporary kitchen and break room decors
- Smudge-free stainless steel panels and black front
- Stainless steel reservoir
- Handle on back for easy transport and placement
- Dual mechanical float system with back-up safety operates even when the power is out
- 3 year limited warranty



Cabinet:

Coated stainless steel panels with black front page and pre-drilled holes for simple cup dispenser installation.

Cold Water Refrigeration Unit:

Convection cooled condenser. Internal, spring mounted, hermetically sealed compressor with automatic overload protector requires no lubrication. Refrigerant is controlled by a capillary tube.

Cold Water Thermostat:

Temperature is controlled by an adjustable thermostat and easily accessible on the rear of the unit.

Cold Water Reservoir:

Durable heavy duty type 300 series stainless steel with external copper refrigerant coil encased in pre-fitted molded plastic foam insulation.

One-Piece Hot Water Tank:

450 watt heating element. One-piece type 300 series stainless steel hot tank is easy to replace or service without breaking soldered refrigeration connections.

Hot Water Capacity:

42 x 6 oz. cups of piping hot water per hour. 1 1/2 quart storage tank.

Hot Water Thermostat:

Fixed thermostat with safety limiter.

Hot Water Safety Faucet:

Self-closing activation requires a two-step action that's easy for adults to use, but protects small children.

Float System:

Dual mechanical floats include a safety lock.

Drip Receptor:

Durable dishwasher safe drip tray lifts out for easy cleaning.

Electrical:

115 volts, 60 hertz. 1/20 hp water cooler compressor. Three wire service cord & polarized plug.

Warranty:

Limited 3-year warranty (within the Continental Limits of the U.S. and Canada). Three years on the sealed refrigeration system, one year on most component parts. Detailed warranty certificate enclosed with each cooler; sample copy available upon request.

PSWSAISHS					
		DEPTH	WIDTH	HEIGHT	WEIGHT
DIMENSIONS	PRODUCT	12.4"	12.0"	43.3"	34.2 lbs
	PACKAGING	14.8"	13.4"	44.7"	39.7 lbs
COLD WATER CAPACITY		ROOM TEMP	WATER TEMP	GALLONS PER HOUR AT 50°F	NUMBER OF 3 OZ. CUPS PER HOUR
		70°F	70°F	1.4	59
		80°F	80°F	1.0	42
		90°F	90°F	0.6	25
		100°F	100°F	0.4	17



WARNING:

Cancer and Reproductive Harm
www.P65Warnings.ca.gov

Specifications are subject to change without notice.