



## TECHNICAL DATA SHEET

### SUPER LUBE® MULTI-PURPOSE SYNTHETIC LUBRICANT WITH SYNCOLON® (PTFE) (AEROSOL)

January 2023

#### PRODUCT DESCRIPTION:

Super Lube® Multi-Purpose Synthetic Lubricant with Syncolon® (PTFE) is a multi-purpose grease in an aerosol form that is safe to use on anything that slides, rolls, swivels or squeaks.

Super Lube® Multi-Purpose Aerosol with Syncolon® (PTFE) is a synthetic, heavy duty lubricant that provides superior wear protection. It penetrates, lubricates and extends the life of machinery and equipment.

Super Lube® Multi-Purpose Aerosol with Syncolon® (PTFE) provides excellent oxidation resistance and rust protection.

Super Lube® Multi-Purpose Aerosol with Syncolon® (PTFE) is a NSF registered Food Grade lubricant, rated H1 for incidental food contact. Meets former USDA (H1) guidelines.



#### FEATURES:

- ❖ Prevents rust and corrosion while reducing friction
- ❖ Provides superior anti-wear performance
- ❖ Penetrates and coats
- ❖ Will not drip, run or evaporate
- ❖ Longer machinery life, reduces maintenance
- ❖ Remains free flowing in freezing temperatures
- ❖ Water and saltwater resistant
- ❖ High dielectric strength
- ❖ NSF Registered (H1), #125824
- ❖ Kosher Certified

#### TYPICAL APPLICATIONS:

<b>Industrial:</b>	Bearings, Conveyors, Chains, Pumps, Open Gears, Machines, Food processing equipment
<b>Automotive:</b>	Calipers, Chassis, Door hinges and locks, Shocks and springs, Trunk latches, Battery protector, Power antennas
<b>Marine:</b>	Snaps, Zippers, Winches and pulleys, Inboard and outboard drives, Prop shafts, Rollers, Sail tracks
<b>Household:</b>	Windows, Locks, Garage doors, Lawnmowers, Pool pumps, Sewing machines, Appliances, Tools, Toys
<b>Recreational and Sporting:</b>	Fishing, Bicycles, RV's, Roller blades, Hunting, Fitness equipment



## TECHNICAL DATA SHEET

### SUPER LUBE® MULTI-PURPOSE SYNTHETIC LUBRICANT WITH SYNCOLON® (PTFE) (AEROSOL)

January 2023

#### PACKAGE SIZES:

Part No.	Description
31040	6 oz. Aerosol
31110	11 oz. Aerosol

#### PROPERTIES:

Test	Rating
NLGI Grade (Base)	2
Color:	Translucent
Temperature range:	-45°F to 450°F (-43°C to 232°C)
Specific gravity:	.866
Odor:	Solvent-like
Type of film:	Non-drying
Lubricating solid:	PTFE
Solvent content VOC (California):	15%

#### DIRECTIONS:

- Clean and dry area to be treated.
- Shake well before using. Use handy extension tube for pinpoint applications.
- Re-apply as necessary.

#### SHELF LIFE / WARRANTY:

Super Lube® products have a five (5) year recommended shelf life when stored in the original container and in reasonable ambient conditions. The warranty period is twenty-four (24) months from the date of purchase. For complete information visit [www.super-lube.com/what-is-the-shelf-life-ezp-320.html](http://www.super-lube.com/what-is-the-shelf-life-ezp-320.html).



See Safety Data Sheet (SDS) for further detail regarding safe use of this product.



The information provided in this Technical Data Sheet including the recommendations for use and application of the product are based on our knowledge and experience of the product as of the date of this bulletin. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Synco Chemical Corporation is, therefore not liable for the suitability of our product for the production processes and conditions in respect for which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

All Super Lube® and Syncolon® trademarks in this document are trademarks of Synco Chemical Corporation.