


Index No	Part Ref	Description	Qty
A	2050547823	REGULATOR ASSEMBLY	
3		REGULATOR	1
4		O-RING 8.1x1.6	1
5		O-RING 8x1	1
6		SPRING RING WR9	1
7		VALVE STEM	1
8		O-RING 2x1	1
B	2050546343	VALVE KIT	
9		TIP VALVE	1
10		SPRING	1
C	2050547893	FRONT PLATE ASSEMBLY	
22		FRONT PLATE	1
23		PIN SPRING 3x4	1
24	6157580520	BEARING 10x26x8	1
25		WASHER	1
D	2050547843	REAR PLATE ASSEMBLY	
23		PIN SPRING 3x4	1
30		REAR PLATE	1
31	6157581390	BEARING 6x19x6 626ZZ	1
E	2050547853	MOTOR ASSEMBLY	
C	2050547893	FRONT PLATE ASSEMBLY	1
D	2050547843	REAR PLATE ASSEMBLY	1
26	6154261220	ROTOR	1
28	2050547793	BLADES (SET OF 4)	1
29	6154001490	CYLINDER	1

	2050544623	EC declaration
	6159948750	Safety instructions
	2050543813	Operator's manual

Index No	Part Ref	Description	Qty
F	2050546413	SMALL PARTS KIT	
6		SPRING RING WR9	1
8		O-RING 2x1	1
12		NEEDLE 2.5x11.8	1
14		O-RING 27x2	1
17		O-RING 17x2	1
19		RING	1
20		SPACER	1
21		O-RING 15.6x1.78	1
	2050547863	TUNE-UP KIT CP3000-4..., CP3030-4..	
2		SEAL	1
16		FELT	1
28	2050547793	BLADES (SET OF 4)	1
22		PAPER GASKET	1
1	2050547813	HANDLE ASSY (incl. Part # 15)	1
11	2050541493	SAFETY LEVER	1
13	6155740750	AIR CONTROL RING 15 000 RPM	1
	6155740700	AIR CONTROL RING 18 000 RPM	1
	6155740710	AIR CONTROL RING 20 000 RPM	1
	6155740730	AIR CONTROL RING 24 000 RPM	1
15		REAR CAP	1
18	2050542533	INLET ASSY	1
27	6156080520	ROTOR NUT	1
32	6154600420	BLOCK PLATE	1
33	6156731420	COVER	1
34	6155260630	COLLET HOLDER 1/4" SIAL 200	1
35	6156071540	COLLET NUT	1
36	2050548193	SPANNER	2

Recommended collets

1/8" (2,4 to 3,2mm) 200 series	6155260610
2-1/4" (5,2 to 6mm) 200 series	6155260620
1/4" (5,55 to 6,35mm) 200 series (included)	6155260630
5/16" (7,2 to 8mm) 200 series	6155260640
3/8" (8,7 to 9,5mm) 200 series	6155260650