



# 12 Piece Metric Punch & Chisel Kit



A professional selection of the most popular Punches & Chisels



- Exact fit metric sizes
- Extra long pins offer the greatest depth of penetration
- Select sizes fit most applications
- Struck ends are tempered to help reduce chipping
- Black oxide finish for additional rust protection & professional appearance
- Heavy duty, full-shank heat treated tool steel for maximum durability & exceptional strength

#### Popular Uses:

Automotive  
Oil  
Gas  
Chemical  
Mining  
Metal Working  
Commercial Construction  
Residential Construction  
Industrial Maintenance

Item	Description	OAL	Body Size	Body Type	Pin Size	Blade Width	Weight (kg/lbs)
10237	7mm Cold Chisel	125mm (4.92")	7mm (1/4")	Hex	N/A	7mm (1/4")	0.03 (0.07)
10243	13mm Cold Chisel	150mm (5.90")	11.1mm (7/16")	Hex	N/A	13mm (1/2")	0.11 (0.25)
10249	19mm Cold Chisel	180mm (7.08")	15.9mm (5/8")	Hex	N/A	19mm (3/4")	0.27 (0.59)
20020	3mm Solid Punch	125mm (4.92")	9.5mm (3/8")	Hex	3mm (1/8")	N/A	0.07 (0.15)
21510	4mm Long Pin Punch	200mm (7.87")	7.9mm (5/16")	Hex	4mm (3/16")	N/A	0.06 (0.13)
21512	5mm Long Pin Punch	200mm (7.87")	9.5mm (3/8")	Hex	5mm (3/16")	N/A	0.78 (0.17)
21514	6mm Long Pin Punch	200mm (7.87")	9.5mm (3/8")	Hex	6mm (1/4")	N/A	0.09 (0.19)
21516	7mm Long Pin Punch	200mm (7.87")	9.5mm (3/8")	Hex	7mm (1/4")	N/A	0.09 (0.20)
21518	8mm Long Pin Punch	200mm (7.87")	11.1mm (7/16")	Hex	8mm (5/16")	N/A	1.24 (2.73)
21519	9mm Long Pin Punch	200mm (7.87")	12.7mm (1/2")	Hex	9mm (3/8")	N/A	0.16 (0.35)
24015	5mm Center Punch	125mm (4.92")	9.5mm (3/8")	Hex	5mm (3/16")	N/A	0.07 (0.15)
24018	8mm Center Punch	150mm (5.90")	12.7mm (1/2")	Hex	8mm (5/16")	N/A	0.15 (0.33)

Always wear safety goggles when using hand tools.



MAYHEW STEEL PRODUCTS, INC., 199 Industrial Blvd., Turners Falls, MA 01376 U.S.A.  
800 872-0037 (US only) • +1 413-863-4860 • Fax: +1 413-863-8464 • www.Mayhew.com

*call us or ask your representative for details!*