



**HBL7777A**

## Weatherproof Covers for Receptacles with Face Dia. of 2.28–2.44 in. (57.9–62.0)

Description	Catalog Number
Thermoplastic, 2-gang, wet and damp locations with cover “closed”, gray.	<b>HBL7777A<sup>▲</sup></b>
Thermoplastic, 2-gang, wet and damp locations with cover “closed”, yellow.	<b>HBL77CM77A<sup>▲</sup></b>

## Weatherproof Covers for Receptacles with Face Dia. of 2.09–2.13 in. (53.1–54.1)

Description	Catalog Number
Cast aluminum, wet locations only when cover “closed” and damp locations.	<b>HBL9420</b>
Cast aluminum, no lift cover. NOT weatherproof.	<b>HBL9419</b>



**HBL9420**

## Weatherproof Covers for 50A Twist-Lock<sup>®</sup> Single Receptacles

Description	Catalog Number
Thermoplastic, wet and damp locations with cover “open”, gray.	<b>HBL7774WO<sup>*</sup></b>
Thermoplastic, wet and damp locations with cover “open”, yellow.	<b>HBL77CM74WO<sup>*</sup></b>
Cast aluminum, wet locations only when cover “closed” and damp locations.	<b>HBL7770</b>
Galvanized Steel, fits 4" square or 2-gang box.	<b>HBL50SC<sup>**</sup></b>
Stainless steel, single gang, wallplate. NOT weatherproof.	<b>SS750<sup>▲</sup></b>



**HBL7774WO**

## Weatherproof Covers for 30A, 4 Wire Hubbellock<sup>®</sup> Receptacles

Description	Catalog Number
Thermoplastic, wet and damp locations with cover “open”, gray.	<b>HBL7428WOG<sup>*</sup></b>
Thermoplastic, wet and damp locations with cover “open”, yellow.	<b>HBL7428WOY<sup>*</sup></b>
Thermoplastic, wet and damp locations with cover “open”, red.	<b>HBL7428WOR<sup>*</sup></b>
Cast aluminum, wet locations only when cover “closed” and damp locations, lift cover plate.	<b>HBL20405</b>
Cast aluminum, wet locations only when cover “closed” and damp locations, red finish.	<b>HBL20446</b>
Cast aluminum, no lift cover. NOT weatherproof.	<b>HBL20406</b>

Note: <sup>▲</sup>Will fit FS/FD boxes having wallplate mounting holes on 3.25 in. x 3.75 in. (82.6 x 95.3) centers.  
<sup>▽</sup>Will only fit old style porcelain face devices.  
<sup>\*</sup>The “CS” versions of 50A Twist-Lock<sup>®</sup> will only fit these wallplates.  
<sup>\*\*</sup>IP20 Suitability.



**HBL7770**

## Weatherproof Covers for Single Receptacles on FS/FD Boxes

All weatherproof covers are UL Listed for WET LOCATIONS WITH COVER CLOSED for intermittent use in wet locations or use in damp locations. Those with suffix “WO” are listed for WET LOCATIONS with cover open in continuous use. All plates are gasketed and self-closing.

## Accessories

Description	Catalog Number
Sub-plate for mounting and weatherproofing flanged devices with mounting centers of 1.76", 1.94" or 2.13" such as HBL7556, HBL4716, etc. when used with a HBL7420 or HBL7425WOA type weatherproof covers.	<b>7452<sup>•</sup></b>
Adapter plate for mounting HBL7423WO, HBL7424WO, HBL7425WOA or HBL7420 covers to standard boxes.	<b>HBL7349<sup>•</sup></b>



Note: <sup>•</sup>Not UL Listed.



**HBL20405**



**HBL7349**



Dimensions in Inches (mm)