

Kraftform Kompakt 60, Imperial, stainless, 17pieces

Kraftform Kompakt 60, 62



EAN:	4013288115720	Size:	155x135x60 mm
Part number:	05071117001	Weight:	510 g
Article number:	KK 60 Stainless Imperial	Country of origin:	CZ
		Customs tariff number:	82079030

- Solution to the extraneous rust problem: fasten stainless screws with stainless tools
- Vacuum ice-hardening provides the required hardness and strength
- Handle/Interchangeable blade system for rapid exchange of the blade
- Rapidaptor technology for rapid bit change
- Storage and transport in a robust belt pouch

Pouch with bits in a length of 89 mm. Includes Kraftform holder 3816 R with Rapidaptor quick-release chuck and multi-component Kraftform handle for low-fatigue working. Stainless design to prevent the formation of extraneous rust.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless_imperial.html

Wera - KK 60 Stainless Imperial
05071117001 - 4013288115720

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

 **3816 R**
05051465001 1 x 1/4" x 119 mm



 **3867/4 TORX® B0**
05071089001 1 x TX 10 x 89 mm
05071090001 1 x TX 15 x 89 mm
05071091001 1 x TX 20 x 89 mm
05071092001 1 x TX 25 x 89 mm
05071094001 1 x TX 30 x 89 mm



 **3840/4 Hex-Plus**
05071105001 1 x 3/32" x 89 mm
05071106001 1 x 1/8" x 89 mm
05071107001 1 x 5/32" x 89 mm
05071108001 1 x 3/16" x 89 mm



 **3851/4**
05071081001 1 x PH 1 x 89 mm
05071082001 1 x PH 2 x 89 mm
05071083001 1 x PH 3 x 89 mm



 **3800/4**
05071080001 1 x 1 x 5.5 x 89 mm



 **3868/4 Square-Plus**
05071097001 1 x # 1 x 89 mm
05071098001 1 x # 2 x 89 mm
05071099001 1 x # 3 x 89 mm



Screw stainless steel together with stainless steel!



Solution to the rust problem: screw stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

Handle/interchangeable blade system



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Chuck-all



The Rapidaptor quick-release chucks hold 1/4" DIN ISO 1173-C 6,3 and E 6,3 as well as Wera series 1 and 4 bits.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless_imperial.html

Wera - KK 60 Stainless Imperial
05071117001 - 4013288115720

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

Rapid-out



Simply push the sleeve forward to change the bit. The spring mechanism lifts the bit off the magnet and unlocks the tool. The bit can be easily removed. The rapid-out function makes it easy to remove even the smallest bits without extra tools.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Storage and transport



The tools can be stored and carried in a robust belt pouch, keeping them always to hand.

Web link

https://products.wera.de/en/kraftform_kompakt_kraftform_kompakt_60_62_kk_60_stainless_imperial.html

Wera - KK 60 Stainless Imperial
05071117001 - 4013288115720

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de