

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-541

Palm coated with INTERCEPT TECHNOLOGY® and ANSELL GRIP™ Technology



Cut



Light Duty

## Lightweight cut-resistant industrial gloves with exceptional grip

- **Enhanced grip:** ANSELL GRIP™ technology and palm coating make for industrial gloves with significant grip
- **Heightened defenses:** HyFlex® 11-541 industrial gloves boast INTERCEPT™ Cut Resistance Technology, for EN and ANSI level 4 cut protection
- **Advanced comfort:** ZONZ™ Comfort Fit yarn and stitching enhance these HyFlex® gloves' comfort, while reducing hand fatigue
- **Reinforced durability:** HyFlex® 11-541 safety gloves achieve EN and ANSI level 4 abrasion resistance thanks to FORTIX™ Abrasion Resistance Technology
- **Added dexterity:** The 11-541's ultralight liner blends personal protection with optimized flexibility
- **Aesthetics and convenience:** These PPE gloves' dirt-masking palm hides stains and they are offered in vend pack form

### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

### Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges



# HyFlex<sup>®</sup>

ADVANCED MECHANICAL PROTECTION

## 11-541

Palm coated with INTERCEPT TECHNOLOGY<sup>®</sup> and ANSELL GRIP<sup>™</sup> Technology

### Key Features

- ANSELL GRIP<sup>™</sup>: Coating treatment minimizing force required
- INTERCEPT<sup>™</sup> Cut Resistance: EN and ANSI level 4 hand protection
- ZONZ<sup>™</sup> Comfort Fit: For PPE gloves boasting comfort and dexterity

### Technologies

 **ANSELL GRIP<sup>™</sup>**  
Ansell Grip Technology

 **FORTIX<sup>™</sup>**  
Abrasion Resistance Technology

 **INTERCEPT<sup>™</sup>**  
Cut Resistance Technology

**Kevlar<sup>®</sup>**



Touchscreen Compatible

 **ZONZ<sup>™</sup>**  
Comfort Fit Technology

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex <sup>®</sup> 11-541	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Foam Nitrile <b>Liner Material:</b> Kevlar <sup>®</sup> , Nylon, Spandex, Stainless steel <b>Cuff Style:</b> Knitwrist	18	6, 7, 8, 9, 10, 11	196-250 mm; 7.71-9.84 inches	Grey	• 12 pairs in a bag; 12 bags in a carton

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

**Ansell**