

12" and 18" Pick Racks & Systems


16-gauge steel high-density parts storage

- Angled shelves keep parts at the front of the bin for easy access
- Available in Single- or Double-Sided units or as a Bench Rack in 12" or 18" depths



APRS18

UP TO
1800
LBS.



APRD182Y



APRBENCH010B

COLOR
Gray



12" Deep Pick Rack 12" D x 36 3/4" W x 60 1/4" H				Shelf Dimensions (in.)		
Model No.	Description	Wt. Capacity (Lbs.)	Caster	D	L	H
APRS	Single-Sided Pick Rack (no bins)	400	–	12-1/8	35-5/8	6-7/16
APRD	Double-Sided Pick Rack (no bins)	800	–	12-1/8	35-5/8	6-7/16
APRDMOBILE	Mobile Kit (Handle & Dolly) for Double-Sided Pick Rack	500	4" x 1 1/2" Polyolefin	–	–	–

18" Deep Pick Rack 18" D x 36 3/4" W x 60 1/4" H				Shelf Dimensions (in.)		
Model No.	Description	Wt. Capacity (Lbs.)	Caster	D	L	H
APRS18	Single-Sided Pick Rack (no bins)	900*	–	18-1/8	35-5/8	6-7/16
APRD18	Double-Sided Pick Rack (no bins)	1800**	–	18-1/8	35-5/8	6-7/16
APRD18MOBILE	Mobile Kit (Handle & Dolly) for Double-Sided Pick Rack	1800	5" x 2" Phenolic	–	–	–

*When anchored to wall and floor. **When anchored to floor.

Bench Rack 12" D x 36 3/4" W x 25" H	
Model No.	Description
APRBENCH	Bench Pick Rack, No Bins



18" Pick Racks have 50% more storage capacity than the 12" deep rack.



Bench Rack sits perfectly on a work table, keeping supplies nearby.



Mobile unit available for both sizes of the Double-Sided Pick Rack.




12" Deep Pick Rack Systems

Shelf Bins




APRS170G

ShelfMax Bins




APRD080B

Indicator Bins



APRS36462B

AkroDrawer Bins




APRD182GRY

System Bins



APRD312R

Shelf Bins



APRBENCH120Y

12" Deep Single-Sided Pick Rack			Bin Dimensions (In.)				
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Colors
APRS110	Rack with Shelf Bins	30110	11-5/8	2-3/4	4	96	B,R,Y,G,W,SC
APRS120	Rack with Shelf Bins	30120	11-5/8	4-1/8	4	64†	B,R,Y,G,W,SC
APRS130	Rack with Shelf Bins	30130	11-5/8	6-5/8	4	40†	B,R,Y,G,W,SC
APRS150	Rack with Shelf Bins	30150	11-5/8	8-3/8	4	32†	B,R,Y,G,W,SC
APRS170	Rack with Shelf Bins	30170	11-5/8	11-1/8	4	24	B,R,Y,G,W,SC
APRS040	Rack with ShelfMax	30040	11-5/8	4-1/8	6	64	B,R,Y,SC
APRS080	Rack with ShelfMax	30080	11-5/8	8-3/8	6	32	B,R,Y,SC
APRS090	Rack with ShelfMax	30090	11-5/8	6-5/8	6	40	B,R,Y,SC
APRS010	Rack with ShelfMax	30010	11-5/8	11-1/8	6	24	B,R,Y,SC
APRSAST00	Rack with ShelfMax	30040 / 30090	See above			32 / 20	B,R,Y,SC
APRS36442B	Rack with Indicator Bins	36442BLUE	11-5/8	4-1/4	4	64†	B
APRS36462B	Rack with Indicator Bins	36462BLUE	11-5/8	6-3/4	4	40†	B
APRS112	Rack with AkroDrawers	31112	11-5/8	11-1/8	4-5/8	24	B,R,Y,GRY,CRY
APRS142	Rack with AkroDrawers	31142	11-5/8	3-3/4	4-5/8	72	B,R,Y,GRY,CRY
APRS162	Rack with AkroDrawers	31162	11-5/8	5-9/16	4-5/8	48	B,R,Y,GRY,CRY
APRS182	Rack with AkroDrawers	31182	11-5/8	8-3/8	4-5/8	32	B,R,Y,GRY,CRY
APRSAST	Rack with AkroDrawers	31142, 31162, 31182	See Above			18 / 24 / 8	B,R,Y,GRY,CRY
APRS312	Rack with System Bins	30312	12	33	5	8†	B,R,Y

Specify color of bins when ordering. †Bonus bins included. B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GRY=Gray, CRY=Crystal Clear.

12" Deep Double-Sided Pick Rack			Bin Dimensions (In.)				
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Colors
APRD110	Rack with Shelf Bins	30110	11-5/8	2-3/4	4	192	B,R,Y,G,W,SC
APRD120	Rack with Shelf Bins	30120	11-5/8	4-1/8	4	128†	B,R,Y,G,W,SC
APRD130	Rack with Shelf Bins	30130	11-5/8	6-5/8	4	80†	B,R,Y,G,W,SC
APRD150	Rack with Shelf Bins	30150	11-5/8	8-3/8	4	64†	B,R,Y,G,W,SC
APRD170	Rack with Shelf Bins	30170	11-5/8	11-1/8	4	48	B,R,Y,G,W,SC
APRD040	Rack with ShelfMax	30040	11-5/8	4-1/8	6	128	B,R,Y,SC
APRD080	Rack with ShelfMax	30080	11-5/8	8-3/8	6	64	B,R,Y,SC
APRD090	Rack with ShelfMax	30090	11-5/8	6-5/8	6	80	B,R,Y,SC
APRD010	Rack with ShelfMax	30010	11-5/8	11-1/8	6	48	B,R,Y,SC
APRDAST00	Rack with ShelfMax	30040 / 30090	See above			64 / 40	B,R,Y,SC
APRD36442B	Rack with Indicator Bins	36442BLUE	11-5/8	4-1/4	4	128†	B
APRD36462B	Rack with Indicator Bins	36462BLUE	11-5/8	6-3/4	4	80†	B
APRD112	Rack with AkroDrawers	31112	11-5/8	11-1/8	4-5/8	48	B,R,Y,GRY,CRY
APRD142	Rack with AkroDrawers	31142	11-5/8	3-3/4	4-5/8	144	B,R,Y,GRY,CRY
APRD162	Rack with AkroDrawers	31162	11-5/8	5-9/16	4-5/8	96	B,R,Y,GRY,CRY
APRD182	Rack with AkroDrawers	31182	11-5/8	8-3/8	4-5/8	64	B,R,Y,GRY,CRY
APRDAST	Rack with AkroDrawers	31142, 31162, 31182	See Above			36 / 48 / 16	B,R,Y,GRY,CRY
APRD312	Rack with System Bins	30312	12	33	5	16†	B,R,Y

Specify color of bins when ordering. †Bonus bins included. B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GRY=Gray, CRY=Crystal Clear.

Bench Rack 12" D x 36 3/4" W x 25" H			Bin Dimensions (In.)				
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Colors
APRBENCH120	Bench Pick Rack with Shelf Bins	30120	11-5/8	4-1/8	4	24	B,R,Y,G,W,SC
APRBENCH150	Bench Pick Rack with Shelf Bins	30150	11-5/8	8-3/8	4	12	B,R,Y,G,W,SC
APRBENCH040	Bench Pick Rack with ShelfMax	30040	11-5/8	4-1/8	6	24	B,R,Y,SC
APRBENCH090	Bench Pick Rack with ShelfMax	30090	11-5/8	6-5/8	6	15	B,R,Y,SC
APRBENCH010	Bench Pick Rack with ShelfMax	30010	11-5/8	11-1/8	6	16†	B,R,Y,SC
APRBENCH312	Bench Pick Rack with System Bins	30312	12	33	5	3	B,R,Y

Specify color of bins when ordering. †Bonus bins included. B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GRY=Gray, CRY=Crystal Clear.


18" Deep Pick Rack Systems

Shelf Bins




APRS18128G

ShelfMax Bins




APRD18048R

Indicator Bins




APRS1836448B

AkroDrawer Bins



APRD18148B

System Bins



APRD18318Y

18" Deep Single-Sided Pick Rack			Bin Dimensions (In.)				
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Colors
APRS18128	Rack with Shelf Bins	30128	17-7/8	4-1/8	4	72‡	B,R,Y,G,W,SC
APRS18138	Rack with Shelf Bins	30138	17-7/8	6-5/8	4	48‡	B,R,Y,G,W,SC
APRS18158	Rack with Shelf Bins	30158	17-7/8	8-3/8	4	36‡	B,R,Y,G,W,SC
APRS18178	Rack with Shelf Bins	30178	17-7/8	11-1/8	4	24	B,R,Y,G,W,SC
APRS18048	Rack with ShelfMax	30048	17-7/8	4-1/8	6	64	B,R,Y,SC
APRS18088	Rack with ShelfMax	30088	17-7/8	8-3/8	6	32	B,R,Y,SC
APRS18098	Rack with ShelfMax	30098	17-7/8	6-5/8	6	40	B,R,Y,SC
APRS18018	Rack with ShelfMax	30018	17-7/8	11-1/8	6	24	B,R,Y,SC
APRS18AST00	Rack with ShelfMax	30048 / 30098	See above			32/20	B,R,Y,SC
APRS1836448	Rack with Indicator Bins	36448BLUE	17-7/8	4-1/8	4	72‡	B
APRS1836468	Rack with Indicator Bins	36468BLUE	17-7/8	6-5/8	4	48‡	B
APRS18148	Rack with AkroDrawers	31148	17-5/8	3-3/4	4-5/8	72	B,R,Y,GRY,CRY
APRS18168	Rack with AkroDrawers	31168	17-5/8	5-9/16	4-5/8	48	B,R,Y,GRY,CRY
APRS18188	Rack with AkroDrawers	31188	17-5/8	8-3/8	4-5/8	32	B,R,Y,GRY,CRY
APRS18118	Rack with AkroDrawers	31118	17-5/8	11-1/8	4-5/8	24	B,R,Y,GRY,CRY
APRS18318	Rack with System Bins	30318	18	33	5	8‡	B,R,Y

Specify color of bins when ordering. ‡Bonus bins included. B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GRY=Gray CRY=Crystal Clear.

18" Deep Double-Sided Pick Rack			Bin Dimensions (In.)				
Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Colors
APRD18128	Rack with Shelf Bins	30128	17-7/8	4-1/8	4	132‡	B,R,Y,G,W,SC
APRD18138	Rack with Shelf Bins	30138	17-7/8	6-5/8	4	84‡	B,R,Y,G,W,SC
APRD18158	Rack with Shelf Bins	30158	17-7/8	8-3/8	4	72‡	B,R,Y,G,W,SC
APRD18178	Rack with Shelf Bins	30178	17-7/8	11-1/8	4	48	B,R,Y,G,W,SC
APRD18048	Rack with ShelfMax	30048	17-7/8	4-1/8	6	128	B,R,Y,SC
APRD18088	Rack with ShelfMax	30088	17-7/8	8-3/8	6	64	B,R,Y,SC
APRD18098	Rack with ShelfMax	30098	17-7/8	6-5/8	6	80	B,R,Y,SC
APRD18018	Rack with ShelfMax	30018	17-7/8	11-1/8	6	48	B,R,Y,SC
APRD18AST00	Rack with ShelfMax	30048 / 30098	See above			64/40	B,R,Y,SC
APRD1836448	Rack with Indicator Bins	36448BLUE	17-7/8	4-1/8	4	132‡	B
APRD1836468	Rack with Indicator Bins	36468BLUE	17-7/8	6-5/8	4	84‡	B
APRD18148	Rack with AkroDrawers	31148	17-5/8	3-3/4	4-5/8	144	B,R,Y,GRY,CRY
APRD18168	Rack with AkroDrawers	31168	17-5/8	5-9/16	4-5/8	96	B,R,Y,GRY,CRY
APRD18188	Rack with AkroDrawers	31188	17-5/8	8-3/8	4-5/8	64	B,R,Y,GRY,CRY
APRD18118	Rack with AkroDrawers	31118	17-5/8	11-1/8	4-5/8	48	B,R,Y,GRY,CRY
APRD18318	Rack with System Bins	30318	18	33	5	16‡	B,R,Y

Specify color of bins when ordering. ‡Bonus bins included. B=Blue, R=Red, Y=Yellow, G=Green, W=White, SC=Clear, GRY=Gray CRY=Crystal Clear.



akro-mils.com

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
 In Canada: Ak-West, Inc. • Tel: 877.979.8940 • Fax: 403.225.1696 • sales@ak-westinc.com • ak-westinc.com