


TOTAL SPORTS FIELD SOLUTION



Seymour Midwest is the leading toolmaker and supplier of choice to many different sports and recreational venues from the amateur to the professional level. The highly trained and passionate professionals who care for these sportscares demand tools of quality and durability. Our line consistently exceeds their expectations.

Midwest Rake aluminum dual purpose rake

- Heavy-duty aluminum 36" head and wrap-around bracing
- 66" powder-coated aluminum handle with vinyl grip



Grainger # 44VM84




WHY A DUAL PURPOSE RAKE?


A Seymour Midwest exclusive. This innovative and versatile tool has two teeth profiles. The short teeth are used for breaking up hard packed clay and grading, while the long teeth are for wet clay and general raking.

Midwest Rake field rake

- Rounded teeth offer smooth non-gouging raking action
- Wrap-around bracing with 36" head
- 66" powder-coated aluminum handle with vinyl grip



Grainger # 44VM54




THE RAKE THE PROS USE...

Engineered to the specifications of landscapers and professional baseball grounds crews, the extended grading edge on this rake was designed specifically for leveling.

Midwest Rake ProTurf lute

- Heavy-duty aluminum head with wrap-around bracing
- 36" head with 66" powder-coated aluminum handle



Grainger # 44VZ18




ON THE FIELDS & SKI SLOPES...

This lightweight, heavy-duty lute combines an engineered head design with our strong wrap-around bracing and is another great infield grooming rake. We use a solid aluminum plug in our head-to-handle connection, unlike the plastic or wood plugs used in many other brands.

Seymour 24" general purpose broom

- 3" durable bristles, super-strong gusset bracing
- 60" straight powder-coated aluminum handle



Grainger # 44VN31



OUR GENERAL PURPOSE BROOMS...

are often flipped for a final dressing of base paths and other skinned areas. These brooms use durable polypropylene bristles, firmly attached to a high quality hardwood shoulder.

Seymour 7' double play monster broom

- 3.5" bristles plus short teeth for breaking up dirt
- A-frame foam padded handle
- Hanging hooks
- Three replaceable bristle rows



Grainger # 44VN46

Seymour 7' monster warehouse drag broom

- 3.5" durable bristles
- A-frame foam padded handle
- Hanging hooks
- Two replaceable bristle rows



Grainger # 44VN47



7' DOUBLE PLAY & 7' STANDARD MONSTER DRAG BROOMS...

we've taken the standard infield drag broom and added a scarifier edge allowing the 7' double play drag broom to perform double duty. It functions as a 7' grooming rake and by simply flipping it over to the bristle side, you have the perfect finishing drag. The 7' Standard Drag Broom is still a great finishing drag, but can also be used as a top dressing broom on greens and tee boxes around the golf course. It also clears dew.



Midwest Rake 17" mound and plate shaper

- Heavy-duty aluminum head and bracing
- 66" powder-coated aluminum handle

Grainger # 44VN03



A UTILITY INFIELDER YOU CAN PLAY EVERYDAY...

The perfect size for restoring the pitching mound to a professional surface, just scarify, level, tamp and repeat. Great for shaving and carving the pitching mound.



Midwest Rake 36" non-absorbent roller squeegee

- Great for turf applications
- 60" ergonomic powder-coated aluminum blue handle
- Replacement rollers

Grainger # 44VT55



ERGONOMICS & PREMIUM HANDLES MATTER!

Our bent "ergonomic" powder-coated aluminum handles allow for a more effective downward and forward pressure which provides more effective head-to-surface contact while promoting comfort and ease of use.



Toolite scoop

- One-piece, injection molded
- 14" x 17" head
- 27" handle with d-grip

Grainger # 44VP21



Seymour grain scoop

- #12 poly head
- 27" fiberglass handle with poly d-grip

Grainger # 44VP20



Seymour loop hoe

- 6" x 4" head
- 60" powder-coated aluminum handle
- Replaceable blade

Grainger # 44VN66



Structron 24" poly leaf rake

- 26 tine 24" poly head
- 51" extra-reach fiberglass handle with comfort cushion grip

Grainger # 44VM11



Seymour half moon turf edger

- 8.75" 12 gauge steel blade with cast-iron socket for maximum durability
- 48" hardwood handle

Grainger # 44VN80



Kenyon 8" all-steel tamper

- 8" x 8" 3/8" steel base plate
- Heavy-duty construction for maximum strength
- 48" steel handle with 12" double-dipped vinyl grip

Grainger # 44VX31



Kenyon 10" all-steel tamper

- 10" x 10" 1/4" steel base plate
- Heavy-duty construction for maximum strength
- 48" steel handle with 12" double-dipped vinyl grip

Grainger # 44VX33



Kenyon 4" x 10" all-steel tamper

- 4" x 10" 1/4" steel base plate
- Heavy-duty construction for maximum strength
- 58" steel handle with 12" double-dipped vinyl grip
- Ideal for trench tamping

Grainger # 44VX35



WHERE CAN I USE A SMALL TAMPER?

The smaller 4" x 10" size is perfect for tight spaces, mounds, plates and trenches and comes with a 58" handle.



Kenyon 8" tamper boot

- 8" x 8" vinyl tamper boot with velcro closure

Grainger # 44VX38



WHAT IS A TAMPER BOOT?

A tamper boot softens the blow and prevents soil from sticking.