



PIG® Burpless® Poly-Coated Steel Drum Funnel

DRM1126 For 20 to 55 gal. Plastic or Steel Drums w/ 2" NPT, 11.25" x 15" x 13"

Patented Burpless design delivers fast, no-splash pouring and one-handed access for easy reg compliance.

- Secure closure helps you meet closed container regs; opens and closes instantly using only one hand
- Patented Burpless design vents during pouring for fast, smooth flow with no dangerous splashback
- Lets you pour without venting through 3/4" bung, a possible closed container reg violation if left open
- Gasket and locking mechanism create a tight seal to help reduce vapor emissions
- Lockable to prevent unauthorized access
- Durable, chemical-resistant powder coat helps ensure long service life
- Multiple lid color options let you segregate drums
- Textured, poly-coated interior adds chemical resistance, resists peeling and rusting
- Low-profile steel drum funnel is perfect for pouring from small containers



| Item# | Description | Dimensions | Weight |
|----------------|--------------------|--------------------------|------------|
| DRM1126-BK-NPT | Black, NPT Threads | 11.25" W x 15" L x 13" H | 12.55 lbs. |
| DRM1126-RD-NPT | Red, NPT Threads | 11.25" W x 15" L x 13" H | 12.55 lbs. |

Metric Equivalent:

| Item# | Description | Dimensions | Weight |
|----------------|--------------------|------------------------------|--------|
| DRM1126-BK-NPT | Black, NPT Threads | 28.6cm W x 38.1cm L x 33cm H | 5.7 kg |
| DRM1126-RD-NPT | Red, NPT Threads | 28.6cm W x 38.1cm L x 33cm H | 5.7 kg |

Specifications

| | |
|------------------------|--------------------------------------|
| Special Feature | Burpless; Vapor Control; Padlockable |
| Style | Steel Drum Funnel |

| | |
|------------------------------------|---|
| Use With | 20 to 55 gal. Plastic or Steel Drums w/ 2" NPT |
| Dimensions | 11.25" W x 15" L x 13" H |
| Brand | PIG |
| Drum Bung Opening | 2" NPT Bung |
| Drum Size | 20 gal.; 30 gal.; 55 gal. |
| Drainage Space | 2.75" H x 10.5" Dia. Draining Area |
| Drum Type | Steel Drum; Poly Drum |
| Flame Arrestor Included | No |
| Lid Type | Latching/Locking Lid |
| Overfill Preventer Included | No |
| Sold as | 1 each |
| Weight | 12.55 lbs. |
| New Pig Patent | 5,676,185 |
| # per Pallet | 48 |
| Composition | Funnel - Powder-Coated Steel Lid Gasket - Polyethylene Foam Bung Gasket - PTFE Poly Coat - Epoxy |
| UNSPSC | 27112902 |
| Pigalog® Page Number | Page 298 |

Metric Equivalent

| | |
|-------------------|------------------------------|
| Dimensions | 28.6cm W x 38.1cm L x 33cm H |
| Weight | 5.7 kg |

Technical Information

Technical Documents

[Polyethylene Foam Gasket for PIG Drum Lids and Funnels](#)

[Poly Coated Burpless® Funnel](#)

[29 CFR 1910.106\(e\)\(2\)\(i\)](#)

[40 CFR 262.15](#)

[40 CFR 262.16\(b\)\(2\)\(iii\)](#)

[40 CFR 262.17\(a\)\(1\)\(iv\)](#)

[40 CFR 264.1086\(c\)\(1\)\(ii\)](#)

