

Weather-Resistant Storage Tube for PIG® Rapid Response DrainBlocker® Drain Cover

PLR700 For PIG® Rapid Response DrainBlocker® Drain Cover

Outdoor drains? Store your PIG Rapid Response DrainBlocker nearby in this weather-resistant tube.

- PVC tube protects your drain cover from rain, snow and damaging UV rays
- Hi-viz storage tube can be wall-mounted to help workers find it fast and get to the spill (wall-mount bracket sold separately)
- Flexible pull-off cap removes easily for fast response
- Lightweight design offers economical protection for your drain cover
- NOTE: Click on the selection chart link below to help choose the best Storage Tube for your DrainBlocker



Item#	Description	Dimensions	Weight
PLR700-16IN	16"	PLR700-16IN-ext. dia. 3" x 16" LPLR700-22IN-ext. dia. 3" x 22" LPLR700-31IN-ext. dia. 4" x 31" LPLR700-37IN-ext. dia. 4" x 37" LPLR700-43IN-ext. dia. 4" x 43" L	PLR700-16IN-0.9 lbs. PLR700-22IN-1.15 lbs. PLR700-31IN-2.05 lbs. PLR700-37IN-2.35 lbs. PLR700-43IN-2.7 lbs.
PLR700-22IN	22"	PLR700-16IN-ext. dia. 3" x 16" LPLR700-22IN-ext. dia. 3" x 22" LPLR700-31IN-ext. dia. 4" x 31" LPLR700-37IN-ext. dia. 4" x 37" LPLR700-43IN-ext. dia. 4" x 43" L	PLR700-16IN-0.9 lbs. PLR700-22IN-1.15 lbs. PLR700-31IN-2.05 lbs. PLR700-37IN-2.35 lbs. PLR700-43IN-2.7 lbs.
PLR700-31IN	31"	PLR700-16IN-ext. dia. 3" x 16" LPLR700-22IN-ext. dia. 3" x 22" LPLR700-31IN-ext. dia. 4" x 31" LPLR700-37IN-ext. dia. 4" x 37" LPLR700-43IN-ext. dia. 4" x 43" L	PLR700-16IN-0.9 lbs. PLR700-22IN-1.15 lbs. PLR700-31IN-2.05 lbs. PLR700-37IN-2.35 lbs. PLR700-43IN-2.7 lbs.
PLR700-37IN	37"	PLR700-16IN-ext. dia. 3" x 16" LPLR700-22IN-ext. dia. 3" x 22" LPLR700-31IN-ext. dia. 4" x 31" LPLR700-37IN-ext. dia. 4" x 37" LPLR700-43IN-ext. dia. 4" x 43" L	PLR700-16IN-0.9 lbs. PLR700-22IN-1.15 lbs. PLR700-31IN-2.05 lbs. PLR700-37IN-2.35 lbs. PLR700-43IN-2.7 lbs.

x 31" LPLR700-37IN-ext. dia. lbs.PLR700-43IN-2.7 lbs.
 4" x 37" LPLR700-43IN-ext.
 dia. 4" x 43" L

PLR700-43IN	43"	PLR700-16IN-ext. dia. 3" x 16" LPLR700-22IN-ext. dia. 3" x 22" LPLR700-31IN-ext. dia. 4" x 31" LPLR700-37IN-ext. dia. 4" x 37" LPLR700-43IN-ext. dia. 4" x 43" L	PLR700-16IN-0.9 lbs.PLR700-22IN-1.15 lbs.PLR700-31IN-2.05 lbs.PLR700-37IN-2.35 lbs.PLR700-43IN-2.7 lbs.
-------------	-----	--	---

Metric Equivalent:

Item#	Description	Dimensions	Weight
PLR700-16IN	16"	PLR700-16IN-ext. dia. 7.6cm x 40.6cm LPLR700-22IN-ext. dia. 7.6cm x 55.9cm LPLR700-31IN-ext. dia. 10.2cm x 78.7cm LPLR700-37IN-ext. dia. 10.2cm x 94cm LPLR700-43IN-ext. dia. 10.2cm x 109.2cm L	PLR700-16IN-.4 kgPLR700-22IN-.5 kgPLR700-31IN-.9 kgPLR700-37IN-1.1 kgPLR700-43IN-1.2 kg
PLR700-22IN	22"	PLR700-16IN-ext. dia. 7.6cm x 40.6cm LPLR700-22IN-ext. dia. 7.6cm x 55.9cm LPLR700-31IN-ext. dia. 10.2cm x 78.7cm LPLR700-37IN-ext. dia. 10.2cm x 94cm LPLR700-43IN-ext. dia. 10.2cm x 109.2cm L	PLR700-16IN-.4 kgPLR700-22IN-.5 kgPLR700-31IN-.9 kgPLR700-37IN-1.1 kgPLR700-43IN-1.2 kg
PLR700-31IN	31"	PLR700-16IN-ext. dia. 7.6cm x 40.6cm LPLR700-22IN-ext. dia. 7.6cm x 55.9cm LPLR700-31IN-ext. dia. 10.2cm x 78.7cm LPLR700-37IN-ext. dia. 10.2cm x 94cm LPLR700-43IN-ext. dia. 10.2cm x 109.2cm L	PLR700-16IN-.4 kgPLR700-22IN-.5 kgPLR700-31IN-.9 kgPLR700-37IN-1.1 kgPLR700-43IN-1.2 kg
PLR700-37IN	37"	PLR700-16IN-ext. dia. 7.6cm x 40.6cm LPLR700-22IN-ext. dia. 7.6cm x 55.9cm LPLR700-31IN-ext. dia. 10.2cm x 78.7cm LPLR700-37IN-ext. dia. 10.2cm x 94cm LPLR700-43IN-ext. dia. 10.2cm x 109.2cm L	PLR700-16IN-.4 kgPLR700-22IN-.5 kgPLR700-31IN-.9 kgPLR700-37IN-1.1 kgPLR700-43IN-1.2 kg
PLR700-43IN	43"	PLR700-16IN-ext. dia. 7.6cm x 40.6cm LPLR700-22IN-ext. dia. 7.6cm x 55.9cm LPLR700-31IN-ext. dia.	PLR700-16IN-.4 kgPLR700-22IN-.5 kgPLR700-31IN-.9 kgPLR700-37IN-1.1 kgPLR700-43IN-1.2 kg

10.2cm x 78.7cm LPLR700-
37IN-ext. dia. 10.2cm x 94cm
LPLR700-43IN-ext. dia.
10.2cm x 109.2cm L

Specifications

Use With	PIG® Rapid Response DrainBlocker® Drain Cover
Color	Hi-Viz Green
Dimensions	PLR700-16IN-ext. dia. 3" x 16" L
Dimensions	PLR700-22IN-ext. dia. 3" x 22" L
Dimensions	PLR700-31IN-ext. dia. 4" x 31" L
Dimensions	PLR700-37IN-ext. dia. 4" x 37" L
Dimensions	PLR700-43IN-ext. dia. 4" x 43" L
Sold as	1 each
Weight	PLR700-16IN-0.9 lbs.
Weight	PLR700-22IN-1.15 lbs.
Weight	PLR700-31IN-2.05 lbs.
Weight	PLR700-37IN-2.35 lbs.
Weight	PLR700-43IN-2.7 lbs.
# per Pallet	PLR700-16IN-308
# per Pallet	PLR700-22IN-252
# per Pallet	PLR700-31IN-154
# per Pallet	PLR700-37IN-154
# per Pallet	PLR700-43IN-126
Composition	100%- PVC tube and caps
UNSPSC	24121502
Pigalog® Page Number	Page 171

Metric Equivalent

Dimensions	PLR700-16IN-ext. dia. 7.6cm x 40.6cm L
Dimensions	PLR700-22IN-ext. dia. 7.6cm x 55.9cm L
Dimensions	PLR700-31IN-ext. dia. 10.2cm x 78.7cm L
Dimensions	PLR700-37IN-ext. dia. 10.2cm x 94cm L
Dimensions	PLR700-43IN-ext. dia. 10.2cm x 109.2cm L
Weight	PLR700-16IN-.4 kg
Weight	PLR700-22IN-.5 kg
Weight	PLR700-31IN-.9 kg
Weight	PLR700-37IN-1.1 kg
Weight	PLR700-43IN-1.2 kg

Technical Information

Technical Documents

Selection Chart for PLR700



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com