

300 Series Irrigation Backflow Preventers

Labor-Saving Flushing, Maintenance, and Repair Solutions Save Time and Money

Safe and Easy Line Flushing and Installation


- EZSwap™ Pressure Vessel is quickly removed and replaced with Flush Fitting Tool (FLUSH) for simple line flushing to remove fouling debris
- Easy single person flushing saves up to **15 minutes** per unit
- Z-Bite™ solderless connections speed installation

Simple Maintenance and Repair

- EZSwap is removed and replaced in seconds, reducing repair cost and down-time
- EZSwap is serviceable off-line and reusable, allowing maintenance and repairs to be performed in the safety of the work truck or shop

Durability

- UV-resistant, reinforced nylon EZSwap resists corrosion and mineral build-up to better withstand harsh outdoor conditions
- Stainless steel shut-off valve handles, hardware, and struts resist corrosion
- Permanent, engraved serial number on strut is long lasting and avoids new registration costs
- Optional black fusion epoxy coating camouflages bronze, virtually eliminating theft



3/4" 375
Reduced Pressure
Principle Assembly



3/4" 350
Double Check
Valve Assembly

Availability

- With multiple regional service centers, Zurn representative warehouses, and local wholesale distribution partners, product is readily available for installation when needed

Lowest Life-Cycle Costs

- Reduced labor and repair kit costs yield savings of **75%** or more over the backflow life-cycle in comparison to other manufacturers



300 Series Irrigation Backflow Preventers

Simple Line Flushing with the EZSwap™ and Flush Fitting Tool

1-1/2" 375XL shown



Backflow is installed with ball valves in the closed position.



Un-bolt or un-screw and remove EZSwap Pressure Vessel.



Drop in and install Flush Fitting Tool.



Attach hose to Flush Fitting Tool and turn on inlet ball valve. Direct water to landscaping or safe drain and flush until clear.



Remove Flush Fitting Tool and reinstall EZSwap Pressure Vessel.



Commission the backflow and start up system.

300 Series Irrigation Part Numbers

REDUCED PRESSURE PRINCIPLE ASSEMBLIES (RP)

SIZE	PART NUMBER
1/2"	12-375
3/4"	34-375
1"	1-375
1-1/4"	114-375
1-1/2"	112-375
2"	2-375

DOUBLE CHECK VALVE ASSEMBLIES (DC)

SIZE	PART NUMBER
1/2"	12-350
3/4"	34-350
1"	1-350
1-1/4"	114-350
1-1/2"	112-350
2"	2-350

375 FLUSH FITTING TOOLS

SIZE	PART NUMBER
1/2"-3/4"	RK34-375FLUSH
1"	RK1-375FLUSH
1-1/4"-2"	RK114-350-375FLUSH

350 FLUSH FITTING TOOLS

SIZE	PART NUMBER
1/2"-3/4"	RK34-350FLUSH
1"	RK1-350FLUSH
1-1/4"-2"	RK114-350-375FLUSH

375 and 350 Approvals

- ASSE® Listed (375XL ASSE 1013, 350XL ASSE 1015)
- IAPMO® Listed
- AWWA Compliant
- (375XL AWWA C511, 350XL AWWA C510)
- CSA® Certified
- Approved by the Foundation for Cross Connection Control and Hydraulic Research at the University of Southern California



Visit our [OneZurn YouTube Channel](#) for the step-by-step flushing, troubleshooting, and repair videos.

ZURN WILKINS 1747 Commerce Way, Paso Robles, CA 93446, 855-663-9876

In Canada: ZURN INDUSTRIES LIMITED 7900 Goreway Drive, Unit 10, Brampton, Ontario L6T 5W6, 905-405-8272

Form No. 480-118, 5/17



US 1.855.ONE.ZURN CANADA 1.905.405.8272 [ZURN.COM](#)