
MLD
MAGNIFIER LUMINAIRE





Strong arm and joint design and materials ensure easy and drift-free positioning.



MLD – PERFECT, FLAWLESS VISION

A perfect combination of optimal 3.5 diopter magnification and high light quality – the MLD magnifying luminaire can be used wherever a closer look is needed. The 2D head joint along with a wide field of vision allow for adjustability with comfort and ease.

The 6.3-inch distortion-free lens and premium LED light offer clear, glare-free vision at the work surface. In addition, the dimming functionality makes this magnifying luminaire an indispensable tool for many industrial applications where intricate work is performed.



- LED technology
- 3.5 diopter magnification
- 6.3-inch diameter magnifying lens made from strong PMMA acrylic
- Ergonomic design with 2D head joint
- Color Rendering Index (CRI) >80
- 5000K color temperature
- Continuously dimmable 100% to 10%
- Strong anodized aluminum housing
- Includes table clamp (0 – 2.7 inches)
- ETL/cETL approved

MOUNTING OPTIONS



Table Clamp
(included)



Wall Mount



Table Base



Rolling Floor Stand

ORDERING INFORMATION

| Wattage | Arm Reach | Magnification | Color Temp | Part # |
|------------------|--------------------------|--------------------|--------------------|--------------------|
| 12 W | 31" | 3.5 diopters | 5000 K | 113525000-00698859 |
| Mounting Options | Item | Dimensions | Part # | |
| | Table clamp (included) | 0" – 2.75" span | ILL00100C-00050472 | |
| | Table base for pin mount | 10" diameter | 190186019-00009644 | |
| | Wall mount | 3.5" x 2.5" x 2.5" | 308218109 | |
| | Rolling Floor Stand | 25" diameter | US1043019 | |

HEADQUARTERS GERMANY

Herbert Waldmann GmbH & Co. KG
Postfach 50 62
78057 VILLINGEN-SCHWENNINGEN

GERMANY

Telephone +49 7720 601-0
Telephone +49 7720 601-100 (Sales)
Fax +49 7720 601-290
www.waldmann.com
sales.germany@waldmann.com

FRANCE

Waldmann Eclairage S.A.S.
Zone Industrielle
Rue de l'Embranchement
67116 REICHESTETT
FRANCE
Telephone +33 3 88 20 95 88
Fax +33 3 88 20 95 68
www.waldmann.com
info-fr@waldmann.com

ITALY

Waldmann Illuminotecnica S.r.l.
Via della Pace, 18 A
20098 SAN GIULIANO MILANESE (MI)
ITALY
Telephone +39 02 98 24 90 24
Fax +39 02 98 24 63 78
www.waldmann.com
info-it@waldmann.com

THE NETHERLANDS

Waldmann B.V.
Lingewei 19
4004 LK TIEL
THE NETHERLANDS
Telephone +31 344 631019
Fax +31 344 627856
www.waldmann.com
info-nl@waldmann.com

AUSTRIA

Waldmann Lichttechnik Ges.m.b.H.
Gewerbepark Wagram 7
4061 PASCHING/LINZ
AUSTRIA
Telephone +43 7229 67400
Fax +43 7229 67444
www.waldmann.com
info-at@waldmann.com

SWEDEN

Waldmann Ljusteknik AB
Skebokvarnsvägen 370
124 50 BANDHAGEN
SWEDEN
Telephone +46 8 990 350
Fax +46 8 991 609
www.waldmann.com
info-se@waldmann.com

SWITZERLAND

Waldmann Lichttechnik GmbH
Benkenstrasse 57
5024 KÜTTIGEN
SWITZERLAND
Telephone +41 62 839 1212
Fax +41 62 839 1299
www.waldmann.com
info-ch@waldmann.com

UNITED KINGDOM

Waldmann Lighting Ltd.
10 Millfield House
Croxley Green Business Park
WATFORD WD18 8Y
Telephone +44 1923 800030
Fax +44 1923 800016
www.waldmann.com
E-Mail info-uk@waldmann.com

USA

Waldmann Lighting Company
9 W. Century Drive
WHEELING, ILLINOIS 60090
USA
Telephone +1 847 520 1060
Fax +1 847 520 1730
www.waldmannlighting.com
waldmann@waldmannlighting.com

CHINA

Waldmann Lighting (Shanghai) Co. Ltd.
199 Changjian Road, Baoshan
SHANGHAI, PRC 200949
Telephone +86 21 5169-1799
Fax +86 21 3385-0032
www.waldmann.com
E-Mail info-cn@waldmann.com

SINGAPORE

Waldmann Lighting Singapore Pte. Ltd.
77A Neil Road
SINGAPORE 088903
Telephone +65 6275 8300
Fax +65 6275 8377
www.waldmann.com
E-Mail sales-sg@waldmann.com