



ASPEN™ 6B

Battery Backpack Vacuum

Finally, affordable battery backpack vacuums that are comfortable

Aspen™ 6B

Go anywhere

Without the hassle of cords, the operator can clean anywhere with a lithium ion powered battery.

Comfort leads to productivity

An ergonomic Deuter® branded hiking harness designed to decrease muscle fatigue and maximize operator comfort and mobility.

Safe, field-proven performance

Enhanced safety features, such as added strain relief, 63 dBA noise level and 4-stage filtration with HEPA means you can clean more safely and protect your investment.



Three no-nonsense features

1. 55 minute runtime



2. 2.5 hour recharge



3. Easily interchangeable battery



Built to be **tough**. Made to be **easy**.



Deuter® Harness

Designed and manufactured by Deuter, the world leader in hiking backpacks.

Adjustable to operator height (operator comfort)

Stabilizer Straps for exact positioning (ergonomics and safety)

Anatomically cut hip belt (ergonomics and operator comfort)

Anatomically shaped shoulder straps (operator comfort)

Breathable mesh provides 3D airflow, reducing operator exertion (productivity and operator comfort)



Tool kits

Base Kit

Two-piece locking aluminum wand with 14 in / 356 mm tools



Standard Telescoping Kit

Chrome telescoping wand with 14 in / 356 mm tools



Premium Sidewinder® Kit

Two-piece anodized aluminum wand with 18 in / 457 mm Sidewinder tools.





REDUCE COST TO CLEAN

- Maximize productivity with new features such as sidewinder tool and ergonomic harness.
- Improve efficiency, mobility and productivity through use of ergonomic backpack vacuum.
- Three tool kit options to suit a variety of cleaning needs.



HEALTH AND SAFETY

- Increased comfort and mobility for operator due to new ergonomic harness.
- Reduce trip/fall hazard with no cord to manage.



IMAGE

- Improve facility image through 4-stage filtration with HEPA.



SUSTAINABILITY

- LEED qualifying CRI certified vacuum maintains air quality through 4-stage filtration with HEPA.

The Nobles Aspen 6B is the smart, reliable choice for your no-nonsense cleaning needs.

Nobles
701 North Lilac Drive
Minneapolis, MN 55422
USA/Canada: +1.800.553.8033
Quebec: +1.800.361.9050
www.nobles.com
nobles@tennantco.com

Aspen™ 6B Specifications	
Vac motor power	408W*
Vacuum motor current	11.35A*
Vacuum motor airflow	70 cfm / 118 m ³ /m
Vacuum motor sealed water lift	65 in / 165 cm
Vacuum motor thermal protection	Thermal protector with auto reset
HEPA filter, standard	High efficiency (99.97%) at 0.3 micron
Vacuum bag capacity	6 qt / 5.7 L
Power Source	36VDC / 10.4 Ah lithium ion battery
Run time	Up to 55 minutes
Charge time	2.5 hours
Vacuum hose length	2-6 ft / 0.61-1.80 m stretch hose included with vacuum
Dimensions	H: 21 in / 533 mm (25 in / 635mm with harness) W: 9.5 in / 241 mm (13 in / 330 mm with harness) D: 7 in / 178 mm (13 in / 330 mm with harness)
Weight	19.0 lbs / 8.62 kg (9.75 lbs / 4.42 kg body, 3.5 lbs / 1.59 kg harness, 5.75 lbs / 2.6 kg battery)
Sound level (operator's ear)	63 dBA
Approvals	ETL
Warranty	See your local representative for warranty information

*Will vary throughout the operation of the machine; averages are shown. UL does not rate these machines in amperage or wattage.

Specifications subject to change without notice.



Carpet and Rug Institute (CRI)
Seal of Approval -
Certified Silver.