



SL-20L®/SL-20LP®

FULL-SIZE, PROFESSIONAL GRADE
RECHARGEABLE FLASHLIGHT

Full-sized, full-feature duty light that delivers a 529 meter beam distance.



SL-20LP available in black, orange and yellow

High, medium, low and strobe:

- High: 450 lumens; 70,000 candela; 529m beam; runs 3.25 hours
- Medium: 225 lumens; 35,000 candela; 374m beam; runs 5 hours
- Low: 60 lumens; 9,000 candela; 189m beam; runs 20 hours
- Strobe for signaling or disorienting: runs 4.5 hours

Optimized electronics provide regulated intensity

IPX4 water-resistant; 1m impact resistance tested

SL-20L: 13.1" (33.3 cm); 1.7 lbs.(.77 kg)
SL-20LP: 13.2" (33.5 cm); 1.3 lbs.(.59 kg)

Limited Lifetime Warranty
Visit streamlight.com for full warranty information

See reverse for system configurations

Item #	Description
SL-20L®	
20705	SL-20L - 230V AC/12V DC - 2 Sleeves
20707	SL-20L - 240V AC/12V DC - 2 Sleeves
20703	SL-20L - 120V/100V AC/12V DC Smart Charge - 2 Sleeves
20701	SL-20L - 120V/100V AC Smart Charge
20702	SL-20L - 12V DC Smart Charge
20700	SL-20L - (WITHOUT CHARGER)
SL-20LP®	
25325	SL-20LP - 230V AC/12V DC - 2 Sleeves - Yellow
25305	SL-20LP - 230V AC/12V DC - 2 Sleeves - Black
25315	SL-20LP - 230V AC/12V DC - 2 Sleeves - Orange
25327	SL-20LP - 240V AC/12V DC - 2 Sleeves - Yellow
25307	SL-20LP - 240V AC/12V DC - 2 Sleeves - Black
25317	SL-20LP - 240V AC/12V DC - 2 Sleeves - Orange
25323	SL-20LP - 120V/100V AC/12V DC Smart Charge - 2 Sleeves - Yellow
25303	SL-20LP - 120V/100V AC/12V DC Smart Charge - 2 Sleeves - Black
25313	SL-20LP - 120V/100V AC/12V DC Smart Charge - 2 Sleeves - Orange
25321	SL-20LP - 120V/100V AC Smart Charge - Yellow
25301	SL-20LP - 120V/100V AC Smart Charge - Black
25311	SL-20LP - 120V/100V AC Smart Charge - Orange
25322	SL-20LP - 12V DC Smart Charge - Yellow
25302	SL-20LP - 12V DC Smart Charge - Black
25312	SL-20LP - 12V DC Smart Charge - Orange
25320	SL-20LP - (WITHOUT CHARGER) - Yellow
25300	SL-20LP - (WITHOUT CHARGER) - Black
25310	SL-20LP - (WITHOUT CHARGER) - Orange

