



**MCR
SAFETY**

6620KV

**Memphis Redcoat Kevlar
Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

The Memphis Redcoat Kevlar® is produced from higher quality resins and plasticizers. The 6620KV is double dipped with PVC and has a 12" gauntlet cuff with a sandy finish palm. The most unique feature is the seamless DuPont™ Kevlar® lining. This cut resistant liner and premium PVC gives you that liquid resistant / cut resistant combo you've been searching for. Actifresh, an antibacterial agent, is used to eliminate odors and promote better hygiene. This tough and flexible PVC glove provides excellent wet and dry grip. Additionally, it provides a good grip for degreasing and petrochemical applications.



FEATURES:

- Russet PVC
- Supported
- Kevlar/Cotton Plaited
- Full Back
- Waterproof

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Cold storage applications, Food service, Material Handling

TECHNICAL DATA FOR: 6620KV

Series	Memphis Redcoat Kevlar
Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Material	PVC
Grade	Industrial Grade
Features	Waterproof
Lining	Kevlar
Thumb Style	Wing

Overall Length	12 in.
EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	3
EN 388 : CE Score - Tear	4

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6620KV

Memphis Redcoat Kevlar

Supported / Dipped gloves

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6620KVL	Large	12.08	5.92	N/A	42.732 lb.	7.122
6620KVM	Medium	11.92	5.52	N/A	38.718 lb.	6.453
6620KVXL	X - Large	12.01	6.25	N/A	43.710 lb.	7.285
6620KVXXL	XX - Large	12.00	6.57	N/A	45.852 lb.	7.642
6620KVXXXL	XXX - Large	12.00	7.60	N/A	52.518 lb.	8.753

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved