

Go Beyond Normal Limits...™


**RITRON**<sup>®</sup>  
WIRELESS SOLUTIONS

# JMX, Analog, PLMR, Portable Radios

Get More Done with JobCom<sup>®</sup> Two-Way Radios!

- Cost-effective VHF & UHF business band two-way radios
- No monthly fees or airtime charges
- Rugged, small, and lightweight
- Loud, easy-to-hear, high output speaker
- Bright, highly visible LED display
- Field programmable frequencies (26VHF, 77UHF), and privacy codes
- License Free business only frequencies (VHF only)
- PC programmable to custom frequencies
- Up to 10 channel capability
- Up to 4 mile range\*

JMX D-Series



\*line-of-sight, no obstructions,  
actual range will vary





**Accessories**



**RHD-6X**  
HEADSET, BEHIND HEAD  
SINGLE EAR, MIC, PTT



**RHD-8X** EARSET, LAPEL MIC W/PTT  
EARBUD W/CLIP



**BC-JMX / BC-A** Battery Charger 110V-240V  
AC-9.5VDC 100mA



**RSM-3XA**  
SPEAKER MIC W/ EARPHONE JACK/ CLIP



**MHC-A**  
HOLSTER W/ CLIP  
LANYARD, SNAP BOTTOM



**BCJS-AD** BATTERY CHARGER ADAPTER  
SINGLE

**BCJS-4AD**  
ADAPTER, 4 UNIT,  
WITH RPS-1B



**BPS-6N-MH** BATTERY, RECHARGABLE , NiMH, 7.5V



**VHF models**

**JMX-141D\*** 1 1/2 Watt Transmit Power Battery Life: 9 Hrs.

Line-of-Sight Range: Up to 2 Miles  
Coverage: Up to 8 Floors or 150,000 sq. ft.

**JMX-146D\*** 2 Watts Transmit Power Battery Life: 9 Hrs.

Line-of-Sight Range: Up to 2-4 Miles  
Coverage: Up to 15 Floors or 250,000 sq. ft.

**JMX-144D\*** 4 Watts Transmit Power Battery Life: 11.3 low/7.4 high Hrs.

Line-of-Sight Range: Up to 2-5 Miles  
Coverage: Up to 20 Floors or 270,000 sq. ft.

**UHF models**

**JMX-441D** 1 Watt Transmit Power Battery Life: 9 Hrs.

Line-of-Sight Range: Up to 2 Miles  
Coverage: Up to 10 Floors or 175,000 sq. ft.

**JMX-446D** 2 Watts Transmit Power Battery Life: 11.9 Hrs.

Line-of-Sight Range: Up to 2-4 Miles  
Coverage: Up to 20 Floors or 275,000 sq. ft.

**JMX-444D** 3 Watts Transmit Power Battery Life: 11.2 low/8 high Hrs.

Line-of-Sight Range: Up to 2-5 Miles  
Coverage: Up to 25 Floors or 280,000 sq. ft.



**Channel Scan** -Channel scan allows multiple channels to be monitored without changing channels.



**NOAA Weather Scan** (VHF models only)  
Find the NOAA weather frequency for your area and select this channel to monitor the local NOAA weather broadcast.



**NOAA Weather Alert** (VHF models only)  
After selecting the NOAA weather frequency for your area and turning the Weather Alert Feature ON, your radio will automatically look for the Emergency Weather Alert broadcast tone. When detected, your radio will revert to the NOAA Weather Emergency broadcast.

**2-Tone Paging Decode** -In systems designed for 2-tone encode paging, JMX 144 /146/444 D-Series radios can function as a pager and a compact 2-way radio. The radio can be programmed to "listen" for specific paging tones and alert the user with a distinct ring and an LED display.

**MURS Certified** (VHF models only)  
No License Required On Specific MURS Frequencies

\*License Free on specific MURS frequencies

Size and Weight Specs -4.75"x 2.2"x 1.43" -11.5 oz with battery.

Each radio includes battery pack, wall charger, flexible antenna, belt clip.

**The JMX D-Series Radio is fully compatible, scalable and can easily be integrated with our other Ritron wireless products!**



VHF/UHF Portable Radios



Liberty Repeater  
2 Watt & 5 Watt Models



Jobcom Base Station  
Wireless Intercom



Callboxes and Call Buttons



LoudMouth Wireless PA System

Go Beyond Normal Limits...™



**Call 800-USA-1-USA**

For the right Wireless Solutions for your communication needs.

P.O. Box 1998 • Carmel, Indiana 46082-1998 •  
317-846-1201 • Fax: 317-846-4978 email:  
ritron@ritron.com • www.ritron.com