

AlphaTec®

ADVANCED CHEMICAL PROTECTION

2000 COMFORT - Model 177

Superior breathable microporous laminate technology, Type 5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 2000 COMFORT - Model 177

Designed for workers in warm environments to provide an optimum balance between comfort and protection.

- Protection - arms, legs and front torso in AlphaTec® 2000 fabric
- Comfortable to wear featuring moisture vapor permeable fabric (“breathable”) to help reduce the risk of heat stress
- Silicone free, critical in spray painting applications
- Anti-static, tested according to EN 1149-5 and AATTC 76

Industries

- Automotive
- Life Sciences
- Food Processing
- Metal fabrication

Applications

- Clean room cleaning and preparing
- Body painting including surface inspection
- Production line support & maintenance
- Cleaning of plant and machines
- Maintenance of plant and machines
- Crime Scene Investigation (CSI)
- Veterinary Services



AlphaTec®

ADVANCED CHEMICAL PROTECTION

2000 COMFORT - Model 177

Superior breathable microporous laminate technology, Type 5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 2000 COMFORT - Model 177

PRODUCT INFORMATION

Product Material	Microporous Polyethylene Laminate nonwoven (hood, arms and legs) and Polypropylene nonwoven with anti-static treatment (back panel)
Design Features	Collar, 2-way front zipper with re-sealable storm flap, finger loops. Elasticated waist, wrists and ankles. Breathable SMS back panel.
Seam Type	Bound Seams
Standards Overview	CE CATEGORY III (Type 5, Type 6, EN 1073-2, EN 1149-5)
Product Reference	2000 COMFORT - Model 177
Sizes	S-6XL (02-10)
Weight	Microporous Polyethylene Laminate nonwoven 63 gsm Polypropylene nonwoven with anti-static treatment 48gsm

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

