

Previously known as: MICROCHEM<sup>®</sup> by AlphaTec<sup>®</sup> 2300 STANDARD - Model 147

### Lightweight and durable chemical protection against a range of inorganic chemicals and biological hazards.

- A good protective barrier to numerous inorganic liquid chemicals including acids and bases
- Lightweight, yet relatively strong and durable
- Designed to protect, typical overall features include respirator fit hood and a zip flap with self-adhesive tape closure
- Highly visible bright yellow for improved worker safety
- Anti-static, tested according to EN 1149-5 & AATCC 76

#### Industries

- Oil and gas
- Life Sciences
- Machinery and Equipment

#### Applications

- Environmental clean-up and remediation
- Assembly and disassembly of large pipes
- Transferring liquids and solids
- Assembling and mounting components



## 2300 STANDARD - Model 147

Medium duty chemical barrier, Type  
5/6 protection

Previously known as: MICROCHEM® by AlphaTec® 2300 STANDARD - Model 147

### PRODUCT INFORMATION

<b>Product Material</b>	Polyethylene on bicomponent Polypropylene/Polyethylene Nonwoven
<b>Design Features</b>	Coverall, 3-piece hood, 2-way front zipper with resealable storm flap and finger loops. Elasticated hood, waist, wrists, ankles and attached socks.
<b>Seam Type</b>	Bound Seams
<b>Product Reference</b>	2300 STANDARD - Model 147
<b>Country Of Origin</b>	China
<b>Sizes</b>	S-6XL (02-10)
<b>Weight</b>	65gsm

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578