



T5 High Output

F24T5/835/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Color Rendering Index (Nom)	
Base	G5 [G5]	LLMF 2000 h Rated	82
Life to 50% Failures Preheat (Nom)	30000 h	LLMF 4000 h Rated	96 %
Features	HO Alto® [High Output Alto]	LLMF 6000 h Rated	95 %
System Description	High Output (HO)	LLMF 8000 h Rated	94 %
LSF Preheat 2000 h Rated	99 %	LLMF 12000 h Rated	93 %
LSF Preheat 4000 h Rated	99 %	LLMF 16000 h Rated	92 %
LSF Preheat 6000 h Rated	99 %	LLMF 20000 h Rated	91 %
LSF Preheat 8000 h Rated	99 %		90 %
LSF Preheat 16000 h Rated	97 %	Operating and Electrical	
LSF Preheat 20000 h Rated	84 %	Power (Rated) (Nom)	22.5 W
		Lamp Current (Nom)	0.295 A
Light Technical		Temperature	
Color Code	835 [CCT of 3500K]	Design Temperature (Nom)	35 °C
Initial lumen (Nom)	1950 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	1700 lm	Dimmable	Yes
Color Designation	White (WH)	Mechanical and Housing	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	87 lm/W	Cap-Base Information	Green [Green Cap]
Correlated Color Temperature (Nom)	3500 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		
Color Rendering Index (Max)	85		
Color Rendering Index (Min)	80		

T5 High Output

Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	24W/835 Min Bipin T5 HO ALTO UNP
EAN/UPC - Product	046677290207

Order code	290205
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927992183522
Net Weight (Piece)	54.000 g
ILCOS Code	FDH-24/35/1B-L/P-G5-16/850


Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
24W/835 Min Bipin T5 HO	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
ALTO UNP					

TL5 HO F24T5/835 HO Alto

Photometric data





LDPB_TL5-HO8_835-Spectral power distribution B/W


LDPO_TL5-HO8_835-Spectral power distribution Colour

T5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram



LDLE_TL5-HO8_0002-Life expectancy diagram

LDLM_TL5-HO8_0001-Lumen maintenance diagram

