



PIG® Burpless® Poly Drum Funnel

DRM1681 For 30 and 55 gal. Plastic Drums w/ 2" Buttress Thread, 13.5" x 16.25" x 13.9"

No-splash Burpless Poly Funnel with built-in overflow preventer chugs as fast as you can pour, without burps!

- Burpless design vents during pouring for fast, smooth flow with no dangerous splashback
- Lets you pour without venting through 3/4" bung
- Designed for use with nonhazardous liquids: coolants, non-flammable oils and water-based liquids
- Built-in overflow preventer stops flow when the drum is almost full to help you avoid messy overfills
- Thick-wall, 100% polyethylene construction resists UV rays, rust, corrosion and most chemicals
- Lockable to prevent unauthorized access
- Multiple lid color options let you segregate drums
- Attached hinged lid won't get lost or separated from funnel
- Brass neck fits 30- and 55-gallon poly drums with buttress threads
- PTFE tape (included) provides an excellent seal between funnel and drum



Item#	Description	Dimensions	Weight
DRM1681-BK	Black	13.5" W x 16.25" L x 13.9" H	6.75 lbs.
DRM1681-RD	Red	13.5" W x 16.25" L x 13.9" H	6.75 lbs.
DRM1681-YW	Yellow	13.5" W x 16.25" L x 13.9" H	6.75 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
DRM1681-BK	Black	34.3cm W x 41.3cm L x 35.3cm H	3.1 kg
DRM1681-RD	Red	34.3cm W x 41.3cm L x 35.3cm H	3.1 kg
DRM1681-YW	Yellow	34.3cm W x 41.3cm L x 35.3cm H	3.1 kg

Specifications

Special Feature	Burpless; Padlockable
Style	Poly Drum Funnel
Use With	30 and 55 gal. Plastic Drums w/ 2" Buttress Thread
Dimensions	13.5" W x 16.25" L x 13.9" H
Brand	PIG
Drum Bung Opening	2" Buttress Bung
Drum Size	30 gal.; 55 gal.
Drainage Space	6.5" H x 9" Dia. Draining Area
Drum Type	Poly Drum
Flame Arrestor Included	No
Lid Type	Hinged Lid
Overfill Preventer Included	Yes
Sold as	1 each
Weight	6.75 lbs.
New Pig Patent	5,676,185; 5,402,835
# per Pallet	24
Composition	Funnel - Polyethylene Bung Insert - Brass
UNSPSC	27112902
Pigalog® Page Number	Page 299

Metric Equivalent

Dimensions	34.3cm W x 41.3cm L x 35.3cm H
Weight	3.1 kg

Technical Information

Technical Documents

LDPE Products

Disclaimers

Flammables Warning

Not for use with flammables (f.p.<141°F/60.5°C).



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com

