


Heavy Duty, Specification Grade Tamper-Resistant Duplex Receptacles

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Perfect for schools, universities, and other institutional applications where safety and performance are critical



Features

- For use in NEC® locations requiring Tamper-Resistant receptacles
- Best-in-class TR mechanism
- Fed-Spec UL listed
- Engineered, Designed, and Assembled in USA
- Tested to UL Hospital Grade test standards for impact resistance and abrupt plug pull-out
- NAFTA and Trade Act Compliant

APPLICATIONS

- Schools and Universities
- Hotels and Convention Centers
- Assisted Living Facilities
- Transportation Centers
- Military Barracks

The Hubbell Tamper-Resistant Mechanism eliminates the frustration and difficulty

experienced using TR receptacles with plugs that have sharp, or bent blades. Hubbell TR receptacles work so well there is virtually no perceptible difference in the feel between these TR receptacles and our conventional non-TR duplexes. Trust Hubbell to deliver Tamper-Resistant protection that feels like it's not even there!

Tamper-Resistant... **NOT** Plug Resistant™












Heavy Duty, Specification Grade Tamper-Resistant Duplex Receptacles



Heavy Duty, Spec. Grade Tamper-Resistant Receptacles




Description	Color	15A 125V	20A 125V
Smooth nylon face,	Black	HBL5262BKTR	HBL5362BKTR
back and side wired,	Blue	HBL5262BLTR	HBL5362BLTR
duplex	Brown	HBL5262TR	HBL5362TR
	Gray	HBL5262GYTR	HBL5362GYTR
	lvory	HBL5262ITR	HBL5362ITR
	Light Almond	HBL5262LATR	HBL5362LATR
	Red	HBL5262RTR	HBL5362RTR
	White	HBL5262WTR	HBL5362WTR



Tamper-Resistant Receptacles

required to have a TR marking on the face visible when installed without a cover plate.







More Tamper-Resistant Receptacles

Hubbell-PRO Hospital Grade • Tamper-Resistant Receptacles

		Duplex		Styl	Style Line® Decorator	
Description	Color	15A 125V	20A 125V	15A 125V	20A 125V	
Smooth nylon face,	Black	8200BKTRA	8300BKTRA	2172BKTRA	2182BKTRA	
back and side wired	Brown	8200TRA	8300TRA	2172TRA	2182TRA	
	Gray	8200GYTRA	8300GYTRA	2172GYTRA	2182GYTRA	
	lvory	8200IVTRA	8300IVTRA	2172IVTRA	2182IVTRA	
	Light Almond	8200LATRA	8300LATRA	2172LATRA	2182LATRA	
	Red	8200REDTRA	8300REDTRA	2172REDTRA	2182REDTRA	
	White	8200WTRA	8300WTRA	2172WTRA	2182WTRA	

Also available in Commercial and Residential Receptacles. * Visit the Hubbell online catalog for more information.



HUBBELL