

# Leica DISTO™ D2

Compact device – long range



## ***Small, handy, versatile!***

This small and handy laser distance meter has a range of 100 m and is equipped with many interesting functions. Measurements out of corners or from edges are no problem with the multi-functional end-piece.

### Featured with:

- Bluetooth® Smart for data transfer to smart phones and tablets
- Multifunctional end-piece to measure out of corners and from edges
- 100 m range
- X-Range Power Technology
- Clear, illuminated 3 line display
- IP 54 dust and splash water protected




- when it has to be **right**

**Leica**  
Geosystems



### Bluetooth® Smart

The latest Leica App DISTO™ sketch is the ideal link between the Leica DISTO™ D110 and a smartphone or tablet. With it you can prepare layouts and drawings, and dimension them precisely.



### Long distances

With the help of the innovative X-Range Power technology this small device can measure long distances of up to 100 m. In addition, this technology ensures optimum measuring performance, i.e. fast and reliable measurements.



### Multifunctional end-piece

Whether measuring out of corners, slots or from edges, with this end-piece you are prepared for all measuring situations. The instrument detects the end-piece automatically, which helps to avoid expensive measuring errors.



### Useful functions

Functions such as addition and subtraction, area and volume calculations make every measurement task child's play. The instrument stores the last 10 measurement results.



### Leica DISTO™ D2

Art. No. 837031

- Leica DISTO™ D2 laser distance meter
- Holster
- Hand loop
- Batteries

### Technical Data

|                         |  |
|-------------------------|--|
| Accuracy, typ.          | ± 1,5 mm   |
| Range                   | 0.05 – 100 m   |
| Measuring units         | m, ft, in  |
| X-Rang Power Technology | ●  |
| Display illumination    | ●  |
| Free App                | iOS, Android   |
| Data interface*         | Bluetooth® Smart                                     |
| Battery life time**     | up to 10'000 measurements,<br>up to 20h of operation |
| Batteries               | type AAA, 2 x 1,5 V                                  |
| Protection class        | IP 54  |
| Dimensions              | 116 x 44 x 26 mm                                     |
| Weight with batteries   | 100 g  |

\*) System requirements and details at [www.disto.com](http://www.disto.com)

\*\*) Reduced in Bluetooth® Smart mode


### Functions

|                      |
|----------------------|
| Distance measurement |
| Addition             |
| Subtraction          |
| Area measurement     |
| Memory (10 results)  |
| Automatic end-piece  |

All illustrations, descriptions and technical specifications are subject to change without prior notice.  
Printed in Switzerland. Copyright Leica Geosystems AG, Heerbrugg, Switzerland, 2016

Leica Geosystems AG  
Heerbrugg, Schweiz  
[www.leica-geosystems.com](http://www.leica-geosystems.com)

Dealer Stamp



Laser class 2  
In accordance with IEC 60825-1



Register your device within 8 weeks of purchase at [www.leica-geosystems.com/registration](http://www.leica-geosystems.com/registration) and extend your no cost period to 3 years.

- when it has to be **right**

**Leica**  
Geosystems