

## 10 Utility Sink, DURASTONE®






Featuring designer-inspired look and a premium finish, the Model 10 is all business when it comes to the task of laundry or utility tub duty. The Model 10 Utility Sink is a great addition to any laundry, utility or work room.

### Features

- Molded using matched metal molds with premium DURASTONE® fiberglass blended with special resins for extra strength and durability
- Extra-deep, 13" self-rimming 17-gallon capacity bowl
- Includes 1½" drain assembly with stopper
- Connects to standard 1½" P-Trap
- Fits standard 21" x 24" cutout for single-bowl sinks
- Accommodates single or dual-handle faucet with 4" or 8" center
- Available in white and bone
- Stain resistant, semi-gloss, colorfast finish; easy to clean


### Code Accepted

- American National Standards Institute (ANSI) Specification Z 124-2017 
- International Association of Plumbing and Mechanical Officials (IAPMO®) – Listed file #0820 
- Warnock Hersey (Canada) – CSA #B45.0 and B45.5 

### Specifications

Dimensions	Length	Width	Depth	Model	Color
Overall	22"	25"	13 ¼"	10	White
Inside Bowl	15 ¾"	21 ¾"	13 ¼"	10BN	Bone
Cutout	21"	24"	–		

**General:** Furnish and install as shown on plans, a Countertop Sink Model 10 as manufactured by E. L. Mustee & Sons, Inc. Shall be molded fiberglass, using matched metal molds under extreme heat and pressure. One-piece molded construction with self-rimming edge. Complete drain assembly. Overall size: 22" x 25" x 13 ¾". Shall meet ANSI Specification Z 124.6. Color: \_\_\_\_\_ (White, Bone).



## 10C Utility Sink, DURASTONE®






Featuring designer-inspired look and a premium finish, the Model 10C is all business when it comes to the task of laundry or utility tub duty. The Model 10C Utility Sink is a great addition to any laundry, utility or work room.

### Features

- Molded using matched metal molds with premium DURASTONE® fiberglass blended with special resins for extra strength and durability
- Extra deep, 13" self-rimming 17-gallon capacity bowl
- Reinforced 3½" drain opening for standard basket drain (not included)
- Connects to standard 1½" P-Trap
- Fits standard 21" x 24" cutout for single-bowl sinks
- Accommodates single or dual-handle faucet with 4" or 8" center
- Available in white and biscuit
- Stain resistant, semi-gloss, colorfast finish; easy to clean


### Code Accepted

- American National Standards Institute (ANSI) Specification Z 124-2017 
- International Association of Plumbing and Mechanical Officials (IAPMO®) – Listed file #0820 
- Warnock Hersey (Canada) – CSA #B45.0 and B45.5 

### Specifications

Dimensions	Length	Width	Depth	Model	Color
Overall	22"	25"	13 ¼"	10C	White
Inside Bowl	15 ¾"	21 ¾"	13 ¼"	10CBT	Biscuit
Cutout	21"	24"	–		

**General:** Furnish and install as shown on plans, a Countertop Sink Model 10C as manufactured by E. L. Mustee & Sons, Inc. Shall be molded fiberglass, using matched metal molds under extreme heat and pressure. One-piece molded construction with self-rimming edge. Complete drain assembly. Overall size: 22" x 25" x 13 ¾". Shall meet ANSI Specification Z 124.6. Color: \_\_\_\_\_ (White, Biscuit).



## 11 Utility/Bar Sink, DURASTONE®






**Form, function and fashion...**the Model 11 Utility/Hobby/Bar Sink delivers all that and more in a premium quality fiberglass sink that will look great wherever it's installed.

### Features

- Molded using matched metal molds with premium DURASTONE® fiberglass blended with special resins for extra strength and durability
- Extra deep, 9 1/2" self-rimming 7-gallon capacity bowl
- Reinforced 3 1/2" drain opening for standard basket drain (not included)
- Connects to standard 1 1/2" P-Trap
- 17"x 20" Size makes it ideal for narrow or cramped countertops
- Accommodates single or dual-handle faucet with 4" or 8" center
- Available in white, bone and biscuit
- Stain resistant, semi-gloss, colorfast finish; easy to clean


### Code Accepted

- American National Standards Institute (ANSI) Specification Z 124-2017 
- International Association of Plumbing and Mechanical Officials (IAPMO®) – Listed file #0820 
- Warnock Hersey (Canada) – CSA #B45.0 and B45.5 

### Specifications

Dimensions	Length	Width	Depth	Model	Color
Overall	20"	17"	10"	11	White
Inside Bowl	15"	14"	19 1/2"	11BN	Bone
Cutout	18 1/2"	15 1/2"	–	11BT	Biscuit

**General:** Furnish and install as shown on plans, a Countertop Sink Model 11 as manufactured by E. L. Mustee & Sons, Inc. Material composition shall be molded fiberglass, using matched metal molds under extreme heat and pressure. One-piece seamless construction with self-rimming edge. 3 1/2" drain opening. Overall size: 20"x 17"x 10". Shall meet ANSI Specification Z 124.6. Color: \_\_\_\_\_ (White, Bone, Biscuit).



## 20 Bar Sink, DURASTONE®






**The Model 20 combines everything you want in home bar sink...**extra deep bowl and a premium finish that will complement even the most upscale faucet set, countertop and cabinetry.

### Features

- Molded using matched metal molds with premium DURASTONE® fiberglass blended with special resins for extra strength and durability
- Extra deep, 8 1/2" self-rimming 3-gallon capacity bowl
- Reinforced 3 1/2" drain opening for standard basket drain (not included)
- Connects to standard 1 1/2" P-Trap
- Fits standard 13 1/2" x 13 1/2" cutout for bar sinks
- Accommodates single or dual-handle faucet with 4" or 8" center
- Available in white, bone, biscuit and sage granite
- Stain resistant, semi-gloss, colorfast finish; easy to clean


### Code Accepted

- American National Standards Institute (ANSI) Specification Z 124-2017 
- International Association of Plumbing and Mechanical Officials (IAPMO®) – Listed file #0820 
- Warnock Hersey (Canada) – CSA #B45.0 and B45.5 

### Specifications

Dimensions	Length	Width	Depth	Model	Color
Overall	15"	15"	7 3/4"	20	White
Inside Bowl	10"	12"	7"		
Cutout	13 1/2"	13 1/2"	–		

**General:** Furnish and install as shown on plans, a Countertop Sink Model 20 as manufactured by E. L. Mustee & Sons, Inc. Shall be molded fiberglass, using matched metal molds under extreme heat and pressure. One-piece molded construction with self-rimming edge. 3 1/2" drain opening. Overall size: 15" x 15" x 7 1/4". Shall meet ANSI Specification Z 124-2017. Color: \_\_\_\_\_ (White).



To reorder, specify ADV-420 (10-19)