

# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID MH BAL 350W M131 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M131-M171
Lamp Type	350W MH
Number of Lamps	1 piece/unit
Circuit Type	SUPER-CWA
Ballast Type	Magnetic HID
Base Model	71A5993A
Core Size	4 1/4 x 4 3/4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI533-H4
Ignitor Temperature Rating	105°C
Capacitor Value	22.5 MFD
Capacitor Catalog Number	7C225P40
Capacitor Requirements	345V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.75 in
Capacitor Height	4.8 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V


Input Frequency	60 Hz
Inp. Current (Open Circuit)	2.2/1.3/1.1/1 A
Input Current (Starting)	2.2/1.3/1.1/1 A
Input Current (Short Circuit)	1.75-2.65/1.0-1.55/0.9-1.35/0.75-1.15 A
Secondary Short Circuit Current	3.25-4 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	270 V
Input Current (Operating) (Nom)	3.4/2/1.7/1.5 A A
Input Power (Nom)	400 W
Rated Lamp Watts	350 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote	2'
Wiring	

## Core & Coil (71A) MH 175W - 450W

Recommended Fuse Value	10/7/5/5 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	240-300 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/C/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data	
Order product name	CORE & COIL HID MH BAL 350W M131 QUAD KIT
EAN/UPC - Product	781087097502
Order code	71A5993001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700535509
Net Weight (Piece)	5.194 kg

### Dimensional drawing



MH BAL 350W M131 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 350W M131 QUAD KIT	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in

