

## Features and Benefits

UL Type 4X

**IP65,66,69k\***  
SUITABILITY



### FD Boxes and Angled Adapters

Hubbell FD boxes and angled adapters are made of high impact resistant material. They are the only NEC<sup>®</sup> compliant box system that has enough wiring room for a 50A Twist-Lock<sup>®</sup> device. The stainless steel mounting and grounding bracket provides corrosion resistance, necessary in direct wash down applications. The FD Boxes are UL Type 4X rated when used with Watertight Lift Covers, i.e. HBL6500 or HBL6700 as well as with a blank plate such as HBL60CM88. The box and angled adapter can either be purchased separately or as a kit. The FD box and Adapter can be used with any single or duplex receptacle up to a 50A Twist-Lock<sup>®</sup>.



#### Housing Design

- 30 cu. in. FD box made of high impact thermoplastic material
- 3/4" NPT and 1" NPT threaded hub options
- Stainless steel mounting/grounding bracket
- External mounting feet, accepts #10 screw



#### Adapter

- 55° angle adapter (15 cu. in.)
- External mounting feet, accepts #8 screw
- Accepts duplex and single receptacles up to a 50A Twist-Lock<sup>®</sup>

### FD Boxes and Angled Adapters

	Description	Catalog Number
Boxes	(2) 3/4" NPT Hubs, FD Box, Yellow	<b>HBL60CM83A</b>
	(2) 3/4" NPT Hubs, FD Box, White	<b>HBL60CM83WA</b>
	(2) 3/4" NPT Hubs, FD Box, Gray	<b>HBL6083</b>
	(2) 1" NPT Hubs, FD Box, Yellow	<b>HBL60CM84A</b>
	(2) 1" NPT Hubs, FD Box, White	<b>HBL60CM84WA</b>
	(2) 1" NPT Hubs, FD Box, Gray	<b>HBL6084</b>
Adapters	55° Angle Adapter, Yellow	<b>HBL60CM55</b>
	55° Angle Adapter, White	<b>HBL60CM55W</b>
	55° Angle Adapter, Gray	<b>HBL6055</b>
Kits	(2) 3/4" NPT Hubs, Box/Adapter Kit, Yellow	<b>HBL60CM83AK</b>
	(2) 3/4" NPT Hubs, Box/Adapter Kit, White	<b>HBL60CM83WAK</b>
	(2) 3/4" NPT Hubs, Box/Adapter Kit, Gray	<b>HBL6083AK</b>
	(2) 1" NPT Hubs, Box/Adapter Kit, Yellow	<b>HBL60CM84AK</b>
	(2) 1" NPT Hubs, Box/Adapter Kit, White	<b>HBL60CM84WAK</b>
	(2) 1" NPT Hubs, Box/Adapter Kit, Gray	<b>HBL6084AK</b>
Covers	Blank Cover Plate, Yellow	<b>HBL60CM88</b>
	Blank Cover Plate, White	<b>HBL60CM88W</b>
	Blank Cover Plate, Gray	<b>HBLP14FS</b>



Note: \*Plug, receptacle and FD box required for IP69K rating.  
Angled adapters are not UL listed or UL Type 4X.

NEC<sup>®</sup> is a registered trademark of the National Fire Protection Association (NFPA).