INDUSTRIAL STORAGE SOLUTIONS
VTC SERIES

# INDUSTRIAL GRADE AMERICAN MADE SINCE 1911

MACHINISTS' CHESTS / MECHANICS' CHESTS / HAND CARRY TOOL BOXES
ROLLER CABINETS / ROLLER CABINETS
VISUAL TOOL CONTROL / ACCESSORIES

MADEUSA






### **TOOLBOARDS / ACCESSORIES**

### **MAGNETIC VINYL TOOL CONTROL SHEETS**


- · Enhance your visual tool control at a glance
- Cutouts made from magnetic colored vinyl let you identify missing tools instantly
- Simply trace tools with an erasable marker, cut out the shapes, & apply to panels
- Cutouts peel off easily for effortless repositioning
- 1/32" thick

PART #	WIDTH	DEPTH	COLOR		
99814	24"	18"	Red		
99815	24"	18"	Blue		
99816	24"	18"	White		
99817	24"	18"	Yellow		



Tools & panels not included






### 50002

2-PANEL STEEL TOOLBOARD SET

- (2) 18" x 36" steel toolboard panels
- · Set covers 9 sq. ft. of wall space
- Hole spacing is 1 ½"



### 4-PANEL STEEL TOOLBOARD SET

- (4) 18" x 36" steel toolboard panels
- Set covers 18 sq. ft. of wall space
- Hole spacing is 1 ½"
- 60-pc Toolholder hook set (99853)

PART #		SPECIFICATION	SPECIFICATIONS								
		WIDTH	DEPTH	HEIGHT	NET / SHIP WT.	SQ. IN.	PANELS	BODY			
50002	<b>2-Panel Steel Toolboard Set</b> (Measurement is each panel)	18"	1/2"	36"	13 / 16 lbs.	1,296	20 ga				
50004	<b>4-Panel Steel Toolboard Set</b> (Measurement is each panel)	18"	1/2"	36"	32 /37 lbs.	2,592	20 ga				

### SEE PAGES 24 AND 25 FOR A LIST OF TOOL HOLDER HOOK SETS AND ACCESSORIES



### **AVAILABLE COLORS**

Customize the color of your products. Simply place one of the abbreviations at the end of the model number.





### **ACCESSORIES**




### 99851

### 10-PC TOOL HOLDER HOOK SET

- · 4 Single Vertical End Hooks
- 2 Single Angled End Hooks
- · 4 Double Vertical End Hooks

Panel not included




### QTY PART NUMBER DESCRIPTION 99851 10 Piece Tool Holder Hook Set 99852 **30 Piece Tool Holder Hook Set 60 Piece Tool Holder Hook Set** 99853 2 8 12 99820 1" Vertical End Hook, Single 2" Vertical End Hook, Single 2 2 5 99821 2 5 99822 3" Vertical End Hook, Single 2 3 5 99823 2-3/8" Angled End Hook, Single 4" Angled End Hook, Single 1 3 99824 1 3 99825 6" Angled End Hook, Single 3 99827 1" Double Hook Vertical End 2 1 1 3 99828 2" Double Hook Vertical End 1 2 99829 2" Double Hook Angled End 1 1 99830 4" Double Hook Angled End 2 99831 1-3/8" Plier Hook 1 2 99832 2-1/8" Plier Hook 2 3 1/2" Single Spring Clip 99833 3 5/8" Single Spring Clip 99834 1 2 99835 3/4" Single Spring Clip 1 2 99836 1" Single Spring Clip 1 1 99839 2-3/8" Ring Hook 99840 17-1/2" Screwdriver Unit 1 1 5/15" Wrench Rack 1 1 99841 4-1/2" Allen Key Unit 99842

### 99852

### 30-PC TOOL HOLDER HOOK SET

- 17 Assorted Single Hooks
- 4 Assorted Double Hooks
- 2 Assorted Plier Hooks
- 4 Assorted Spring Clips
- 1 Ring Hook, Screwdriver Unit, & Wrench Rack

Panel not included




### 99853

### 60-PC TOOL HOLDER HOOK SET

- · 33 Assorted Single Hooks
- 9 Assorted Double Hooks
- 4 Assorted Plier Hooks
- 10 Assorted Spring Clips
- 1 Ring Hook, Screwdriver Unit, & Wrench Rack
- 1 Allen Key Unit

Panel not included



# **TOOLBOARD ACCESSORIES**







99846



99848



99842




99847

PART #	DESCRIPTION	SPECIFICATIONS				PRODUCT FEATURES				
		WIDTH	DEPTH	HEIGHT	CAPACITY					
99840	Toolboard 12-Screwdriver Rack	17-3/4"	3/4"	1-1/2"	10 lbs.	Stores up to 12 screwdrivers, chisels or files				
99841	Toolboard 8-Wrench Rack	5-1/2"	7″	1-3/4"	15 lbs.	Stores up to 8 SAE or metric combination wrenches				
99842	Toolboard 9-Key Hex Wr. Rack	4-1/2"	1"	3-1/2"	5 lbs.	Stores up to 8 SAE or metric hex wrenches				
99846	Toolboard Parts Shelf	17-1/2"	6-3/4"	4"	40 lbs.	Supports up to 40 lbs.				
99847	4" W Storage Bin Support	4"	3/4"	3″	20 lbs.	Supports multiple bin sizes (Bins sold separately)				
99848	17-3/4" W Storage Bin Support	17-3/4"	3/4"	3″	40 lbs.	Supports multiple bin sizes (Bins sold separately)				

# **TOOLBOARD ACCESSORIES**





PART#	DESCRIPTION	UNIT		INSIDE BE		END		PRODUCT FEATURES		
		WIDTH	DEPTH	HEIGHT	DIAM.	WIDTH	ANGLE	HEIGHT	CAPACITY	
99820	1" Toolboard Hook w/60° end, 10 pc.	3/4"	1"	2 3/8"	1/4"	-	60°	5/8"	20 lbs.	Const. of 1/4" diam. wire
99821	2" Toolboard Hook w/70° end, 10 pc.	3/4"	2"	2 3/8"	1/4"	-	70°	3/4"	20 lbs.	Const. of 1/4" diam. wire
99822	3" Toolboard Hook w/70° end, 10 pc.	3/4"	3"	2 3/8"	1/4"	-	70°	3/4"	20 lbs.	Const. of 1/4" diam. wire
99823	2 1/2" Toolboard Hook w/10° end, 10 pc.	3/4"	2 3/8"	2 3/8"	1/4"	-	10°	5/8"	20 lbs.	Const. of 1/4" diam. wire
99824	4" Toolboard Hook w/10° end, 10 pc.	3/4"	4"	2 3/8"	1/4"	-	10°	3/4"	20 lbs.	Const. of 1/4" diam. wire
99825	6" Toolboard Hook w/10° end, 10 pc.	3/4"	6"	2 3/8"	1/4"	-	10°	3/4"	20 lbs.	Const. of 1/4" diam. wire
99827	1" Toolboard Double Hook w/50° end, 10 pc.	2 1/4"	1"	2 3/8"	1 3/8"	1 1/4"	50°	5/8"	40 lbs.	Const. of 1/4" diam. wire
99828	2" Toolboard Double Hook w/50° end, 10 pc.	2 1/4"	2"	2 3/8"	1 3/8"	1 1/4"	50°	5/8"	40 lbs.	Const. of 1/4" diam. wire
99829	2" Toolboard Double Hook w/10° end, 10 pc.	2 1/4"	2"	2 3/8"	1"	1 1/4"	10°	5/8"	40 lbs.	Const. of 1/4" diam. wire
99830	4" Toolboard Double Hook w/10° end, 10 pc.	2 1/4"	4"	2 3/8"	1"	1 1/4"	10°	5/8"	40 lbs.	Const. of 1/4" diam. wire
99831	1 3/8" W Toolboard Plier Hook, 10 pc.	2 1/4"	1 1/4"	2 3/8"	-	1 1/2"	-	-	40 lbs.	Const. of 1/4" diam. wire
99832	2 1/8" W Toolboard Plier Hook, 10 pc.	2 1/4"	1 1/4"	2 3/8"	-	2 1/8"	-	-	40 lbs.	Const. of 1/4" diam. wire
99833	1/2" Diam. Toolboard Spring Clip, 10 pc.	3/4"	2"	2 3/8"	3/8"	-	-	-	3 lbs.	Holds tools up to 3 lbs.
99835	3/4" Diam. Toolboard Spring Clip, 10 pc.	3/4"	2"	2 3/8"	5/8"	-	-	-	3 lbs.	Holds tools up to 3 lbs.
99836	1" Diam. Toolboard Spring Clip, 10 pc.	3/4"	2"	2 3/8"	1"	-	-	-	3 lbs.	Holds tools up to 3 lbs.
99839	2 3/8" Diam. Toolboard Ring Hook, 2 pc.	2 1/4"	3"	2 3/8"	2 3/8"	-	-30°	2 3/8"	40 lbs.	Const. of 1/4" diam. wire
99876	6" Loop-Hook w/vertical end, 5 pc.	2 1/4"	6"	2 3/8"	-	1 1/4"	75°	2"	20 lbs.	Const. of 1/4" diam. wire

# OPEN. CLOSE. & GET THE JOB DONE.

KENNEDY

A1000 REV 09/2018

1260 Industrial Drive, Van Wert, OH 45891

CQT Kennedy LLC dba Kennedy Manufacturing Co.

800-413-8665 | KennedyMFG.com | custserv@kennedymfg.com