




**S.U.R.&R.**  
Vehicle Fluid Line Repair Solutions

**SPECIALTY**

# FT351

## High Speed Super Duty Flaring Tool

**CONSISTENT,  
HIGH QUALITY  
FLARES**



**Strikes tube center  
perfectly, every time**


## Produce OEM Quality Flares In Seconds

- Creates 45° bubble and double flares including DIN
- Cam lever operation provides speed and efficiency
- Use with ULTRABend, stainless steel and poly-coated lines
- Includes 4 die sets and 7 punches
- Sizes 3/16", 1/4", 5/16", 3/8" and 4.75 mm
- Additional tooling available for 1/2" & 37° flares


## Create Virtually Any Flare Instantly



**SAE single  
(Bubble)**




**SAE  
(Double)**



**DIN single  
(Mushroom)**



"Dial-A-Size" turret



High-speed  
cam lever



A perfect flare  
every time

1.800.390.3996 • phone: 330.745.3300 • fax: 330.745.3488 • [www.surrauto.com](http://www.surrauto.com)

S.U.R.&R. AUTO PARTS INC. • 1969 S. MAIN ST. • AKRON, OH 44301

Rev 0 9/16

# FT351 AVAILABLE ACCESSORIES

CONSISTENT,  
HIGH QUALITY  
FLARES

All items included in **FT351 Kit**


IMAGE	PART#	DESCRIPTION	QTY
	FT205	Die: 3/16"/4.75 mm – 45°	1
	FT210	Die: 1/4" – 45°	1
	FT215	Die: 5/16" – 45°	1
	FT220	Die: 3/8" – 45°	1
	FT225	Die: 1/2" – 45°	1
	FT230	Die: 6 mm – 45°	1
	FT235	Die: 8 mm – 45°	1
	FT240	Die: 10 mm – 45°	1
	FT245	Die: 3/16"/4.75 mm – 37°	1
	FT250	Die: 1/4" – 37°	1
	FT255	Die: 5/16" – 37°	1
	FT260	Die: 3/8" – 37°	1
	FT265	Die: 1/2" – 37°	1
	FT285	Die: 3/16" – DIN	1
	FT290	Die: 1/4" – DIN	1

IMAGE	PART#	DESCRIPTION	QTY	
	FT405	Punch: 3/16"/4.75 mm – 37° & 45° Op. 1	1	
	FT410	Punch: 1/4"/6 mm – 37° & 45° Op. 1	1	
	FT415	Punch: 5/16"/8 mm – 37° & 45° Op. 1	1	
	FT420	Punch: 3/8"/10 mm – 37° & 45° Op. 1	1	
	FT425	Punch: 1/2" – 37° & 45° Op. 1	1	
	FT430	Punch: 3/16" – DIN	1	
	FT435	Punch: 1/4" – DIN	1	
		FT483	Punch: Tube Stop	1
		FT505	Punch: 3/16"/4.75 mm, 1/4"/6 mm – 45° Op. 2	1
	FT510	Punch: 5/16"/8 mm, 3/8"/10 mm – 45° Op. 2	1	
	FT515	Punch: 1/2" – 45° Op. 2	1	
	FT520	Punch: 3/16"/4.75 mm, 1/4"/6 mm – 37° Op. 2	1	
	FT525	Punch: 5/16"/8 mm, 3/8"/10 mm – 37° Op. 2	1	
	FT530	Punch: 1/2" – 37° Op. 2	1	
	FT710	Blank Turret	1	

1.800.390.3996 • phone: 330.745.3300 • fax: 330.745.3488 • [www.surrauto.com](http://www.surrauto.com)