


The Beltrac® Tempest

The all-weather outdoor stanchion built for strength and endurance.

Twist-on Signage

Quickly add standard or custom signage to any Tempest post with a simple twist and click. Available in 3 sizes.



Superior Strength Post

Weatherproof HDPE (High Density PolyEthylene) plastic post is lightweight, yet its superior strength and durability withstands even the harshest environments. Available in 3 colors.



Belt Imprinting

Standard or custom graphics visibly display your message or warning to the public. Available with 2 standard safety messages or 15 high-visibility belt colors. Custom messages upon request.



Integrated Post Handle

Easily pick up the post with the ergonomically placed handle, which provides the correct leverage to handle and move the post short distances.




Eco-friendly Recycled Rubber Base

Non-toxic, recycled rubber means there are no waste by-products, no dangerous chemicals, and no hazardous emissions from the production of the base. And it looks pretty good, too.



Slide and Snap Base Connection

A strong and rigid post-to-base connection keeps the post straight and upright in even the most demanding conditions. Easily disassembles for storage.



Products for People and the Places They Go®

27810 Avenue Hopkins | Valencia, CA 91355
877.ASK.LAVI | 877.275.5284 | 661.257.7800
sales@lavi.com | www.lavi.com

The Beltrac® Tempest

The all-weather outdoor stanchion built for strength and endurance.



Part Number	Color	Belt Colors	Belt Length	Dimensions	Weight	Post Material	Base Material
80-5000R/OR	Orange	15 high-visibility colors PLUS choice of 2 safety messages. <i>Custom messages available.</i>	12 feet	38 ¼ inches tall, 16 wide at base	16 lbs.	HDPE Plastic	Recycled Rubber
80-5000R/YL	Yellow						
80-5000R/BK	Black						

All Tempests come with a 1-Year warranty on post and belt mechanisms.

Standard belt colors and messages:



Please Do Not Enter • Temporarily Closed

Please Do Not Enter • Temporarily Closed (Single-Sided Printing)


Caution • Please Do Not Enter

Caution • Please Do Not Enter (Single-Sided Printing)

Tempest Signage

Add important messaging to your queue or barrier.

- Easy to install. Just twist and click.
- Available in 3 sizes: 7" x 11", 8.5" x 11", and 11" x 14", each ¼" thick.
- Standard messaging or create your own.



STANDARD*						CUSTOM*					
Enter	Exit	Do Not Enter	Please Wait Here	Caution	Custom Message						
7 x 11	80-1130TV/P1S	7 x 11	80-1130TV/P2S	7 x 11	80-1130TV/P3S	7 x 11	80-1130TV/P4S	7 x 11	80-1130TV/P5S	7 x 11	80-1130TV/CPS
8.5 x 11	80-1141TV/P1S	8.5 x 11	80-1141TV/P2S	8.5 x 11	80-1141TV/P3S	8.5 x 11	80-1141TV/P4S	8.5 x 11	80-1141TV/P5S	8.5 x 11	80-1141TV/CPS
11 x 14	80-1131TV/P1S	11 x 14	80-1131TV/P2S	11 x 14	80-1131TV/P3S	11 x 14	80-1131TV/P4S	11 x 14	80-1131TV/P5S	11 x 14	80-1131TV/CPS

*All Tempest Signage is single-sided.