

AVAILABLE THROUGH

GRAINGER[®]

FOR THE ONES WHO GET IT DONE

GRAINGER.COM[®] | 1.800.GRAINGER

EMERGENCY PREPAREDNESS



Emergency back-up cooling when you need it most.

MovinCool units provide true air-conditioning on casters that can be quickly deployed in a variety of emergency situations. Reduce heat stress on equipment and people to keep critical operations up and running.

Applications

- **Emergency Portable Structures** – quick deployment for tents, mobile clinics, or temporary shelters.
- **Flooding** – for emergency drying, high-volume warm air extracts moisture faster than fans or dehumidifiers alone.
- **Heat wave** – reduce the chances of heat stress in hot workspaces and factories, preventing potential OSHA violations.
- **Hurricane/Tornado** – portable a/c solutions that can run from a generator during a power outage or natural disaster.
- **Server/Equipment room failure** – protect heat sensitive equipment and prevent operations from shutting down due to main a/c system failure where redundancy is critical.



Roll it in. Set it up. Turn it on.

Ideal for ...

Healthcare* – Hospitals,
Nursing Homes, Pharmacy,
Doctors offices
Government/Municipalities
Offices/retail
Schools/Universities
Manufacturing

Another line of quality products by DENSO.

DENSO

*MovinCool units are manufactured for general purpose use to control the temperature of the environment. While they contain both condenser and evaporator intake air filters, they do not incorporate any medical grade filters (ie, HEPA) or purification features. If using in a healthcare or medical setting, your facilities management professional should confirm that use of these units is appropriate and will meet applicable health-related requirements.

AVAILABLE THROUGH

GRAINGER[®]

FOR THE ONES WHO GET IT DONE

GRAINGER.COM[®] | 1.800.GRAINGER

MovinCool brings you the best in portable spot air conditioning with the all-new Climate Pro[®] and Classic product series to meet your every need.



Climate Pro K Series

For Healthcare, Laboratory, Office, Retail, Schools, and Server/Telecom Rooms

K12	K18	K24	K36	K60	K63
12,000 Btu/h	16,800 Btu/h	24,000 Btu/h	36,000 Btu/h	60,000 Btu/h	60,000 Btu/h
115 V, 15 amps	115 V, 20 amps	208/230 V, 20 amps	208/230 V, 30 amps	208/230 V, 50 amps	460 V, 20 amps
Grainger SKU: 54ZV21	Grainger SKU: 54ZV22	Grainger SKU: 54ZV23	Grainger SKU: 54ZV26	Grainger SKU: 54ZV27	Grainger SKU: 54ZV28



Climate Pro X Series

For Warehouse, Manufacturing, Outdoors and Moisture Removal

X14	X20	X26
13,200 Btu/h	16,800 Btu/h	24,000 Btu/h
115 V, 15 amps	115 V, 20 amps	208/230 V, 20 amps
Grainger SKU: 54ZV24	Grainger SKU: 54ZV31	Grainger SKU: 54ZV25



Classic Series

For Large Zone Areas in Factories, Warehouse, and Outdoors

Classic 40	Classic 60
39,000 Btu/h	60,000 Btu/h
220 V, 25 amps	460 V, 20 amps
Grainger SKU: 5JLJ7	Grainger SKU: 5JLJ4



Climate Pro D Series

For Heating and Cooling

D12		D18	
Cooling:	Heating:	Cooling:	Heating:
11,450 Btu/h	9,900 Btu/h	15,500 Btu/h	13,100 Btu/h
115 V, 15 amps	115 V, 15 amps	115 V, 20 amps	115 V, 20 amps
Grainger SKU: 54ZV29		Grainger SKU: 54ZV30	

Contact your Grainger Representative or visit Grainger.com

MOVINCOOL[®]

*Btu/h specifications shown with 230 V. Amperage shown with recommended fuse size.

All specifications subject to change without notice.

© 2020 DENSO Products and Services Americas, Inc. | MovinCool and Climate Pro are registered trademarks of DENSO. | MC-EP-SS-0520-GR

