



PIG® Emergency Eye Wash Station Safety Message Mat

GRPWS3511 3' x 5', 2 pads

Combines a hi-viz Emergency Eye Wash Station message with a high-traction, non-slip, adhesive-backed mat to help prevent slips, trips and falls.

- Adhesive-backed mat sticks to the floor without shifting, bunching or tripping up workers; hi-viz Emergency Eye Wash Station image identifies workplace caution
- Large 20" safety image alerts employees to safety requirements or cautions in their workplace
- Absorbent and high-traction top layer removes liquid and debris from shoes and prevents falls in wet, oily work environments
- 5 feet of walk-off coverage prevents dirt, grime and moisture from being tracked around, keeping surrounding floors clean and dry
- Message mat is durable enough to withstand heavy foot traffic, forklifts and pallet jacks
- Absorbs a wide variety of liquids including water, oil and grease; leakproof backing prevents liquid from soaking through to the floor
- Peels up easily without leaving a residue; simply replace when mat shows signs of wear
- Easy to clean; message mat won't shift or be damaged by mops, vacuums, shop/wet vacs or floor scrubbers
- Sticks to most floor surfaces including concrete, VCT, linoleum, ceramic tile, quarry tile and laminate flooring



Item#	Description	Dimensions	Weight
GRPWS3511-BK	Black	3' W x 5' L	4.3 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
GRPWS3511-BK	Black	91.4cm W x 152.4cm L	2 kg

Specifications

Traffic	Heavy Foot Traffic; Carts & Equipment
Indoor/Outdoor	Indoor Use

Pad Quantity	(2) 3' x 5' pads per roll
Incinerable	Yes
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Oils, Coolants, Solvents, Water – Universal
Dimensions	3' W x 5' L
Absorbency	Up to 1 gal. per roll
Absorbency per	Up to .5 gal. per pad
Brand	PIG
Category	Emergency Equipment
Core Diameter	3"
Industry	Industrial Facilities; Shops & Garages
Legend	Emergency Eye Wash Station
Walking Surface	Absorbent Top
Sold as	2 pads per roll
Weight	4.3 lbs.
# per Pallet	42
Composition	Absorbent - Polypropylene Adhesive Backing - Proprietary Adhesive Material
UNSPSC	47131901
UV Resistant	No
Pigalog® Page Number	Page 231

Metric Equivalent

Absorbency per	Up to 1.9 L per pad
Absorbency	Up to 3.8 L per roll
Dimensions	91.4cm W x 152.4cm L
Weight	2 kg

Technical Information

Certifications, Approvals and Ratings

ADA Compliant,NFSI Certified,ANSI B101.1- 2009

Technical Documents

[PIG Adhesive-Backed Mats](#)

[New Pig Adhesive-Backed Mat Notice](#)

[PIG® Grippy® Floor Mats](#)

[29 CFR 1910.22\(a\)\(2\)](#)

Disclaimers

[Safety Instructions Regarding Flammable Liquids for Flame Resistant Mats](#)

Pig Absorbent Mats are flame resistant in their unused state, but take on the properties of flammable liquids they absorb. Always take proper precautions against potential ignition in handling and disposal of these mats if they have absorbed flammable liquids. For further assistance, please call Technical Services.

Color Variation Statement

It is normal for top layer materials to show minor variations in color between production runs. This is particularly true for the grades of materials used in consumable or disposable products such as our adhesive-backed mats. New Pig makes every effort to achieve consistent color, but some variance is possible. Perceived differences in color may also result from mat layout orientation or uneven traffic wear patterns.



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com