

Brady B-514 Floor Marking Graphics

TDS No. B-514

Effective Date: 02/17/2021

Description:

Brady B-514 is a surface printed polyester with a rigid, clear polyester overlamine

Details:



Use:

Brady B-514 is used to mark aisles, passageways, storage locations, point out safety equipment and exits, and enforce protective equipment requirements.

Adhesive Type:

Permanent rubber based adhesive

Substrate Type:

Polyester

Standard Material Colors:

Solid: Black, White, Red, Green, Blue, Yellow, Orange, Purple, Brown, Grey

Striped: Orange/Black, Yellow/Black, White/Black, Red/White, Red/Yellow, Green/White, Blue/Yellow

Checkered: Black/White, Red/White

Thickness:

0.008 in. (0.20 mm)

Adhesive Properties:

Adhesion to Stainless Steel (PSTC-101)

15 Minute Dwell (Avg.) – 155 oz/in (16.9 N/10 mm)

Ultimate Dwell (72 hrs.) (Avg.) – 158 oz/in (17.2 N/10 mm)

Tack (ASTM D2979) (Avg.) = greater than 1000 g

Abrasion Resistance (ASTM D4060):

H-22 Harsh Calibrade Wheels, 1000g wts.

Material withstands up to 2000 cycles

Gloss (20°):

69 units

Minimum Application Temperature:

50°F (10°C)

Service Temperature:

0°F to 140°F (-18°C to 60°C)

Average Outdoor Durability:

Not recommended for outdoor use.

Chemical Resistance:

Reagent	7 day Immersion Impact to Print	7 day Immersion Impact to Adhesive
25% Sulfuric Acid	NE	NE
10% Sulfuric Acid	NE	NE
30% Hydrochloric Acid	NE	NE
10% Hydrochloric Acid	NE	NE
Glacial Acetic Acid	F	F
10% Acetic Acid	NE	NE
50% Sodium Hydroxide	F	NE
10% Sodium Hydroxide	F	NE
10% Ammonia	NE	F
5% Sodium Hypochlorite	NE	NE
10% Sodium Chloride	NE	NE
Methyl Ethyl Ketone	F	F
Acetone	F	F
Toluene	NE	F
Methanol	NE	F
Isopropyl Alcohol	NE	F
Heptane	NE	F
Mineral Spirits	NE	F
Turpentine	NE	F
Diesel Fuel	NE	F
Kerosene	NE	F
Gasoline	NE	F
ASTM # 3 Oil	NE	NE
SAE 20 Oil	NE	NE
Alconox® Detergent	NE	NE
Deionized Water	NE	NE

NE = No Effect

F = Failed (affected Sample)

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

ASTM: American Society for Testing and Materials (U.S.A.)

Alconox® is a registered trademark of Alconox Co.

All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units

PSTC: Pressure Sensitive Tape Council (U.S.A.)

SAE: Society of Automotive Engineers

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2017 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289