

PIG® High-Visibility Safety Floor Runner

GRPSB36200 36" x 100', 1 roll



Provide a no-slip path in hazardous walking areas with our super-safe, adhesive-backed absorbent runner — its hi-viz yellow safety edges can't be missed!

- Tapes and paints are easy to see but do nothing to create a safer floor surface. The PIG High-Visibility Safety Floor Runner is the only floor safety solution that combines a high-traction walking surface with a hi-viz safety edge pattern
- Adhesive backing keeps mat exactly where you put it with no shifting, bunching up or flipping over; traps dirt, salt and moisture to keep it from being tracked around
- Highly visible yellow and black marking is designed to meet ANSI standard for floor markings and help you comply with OSHA 1910.22 (walking surfaces standard)
- Durable printed surface withstands industrial wear and tear; even forklift traffic
- Mat is highly absorbent, quick-drying, very low profile, extremely durable and effortless to maintain
- Easy to use and customize: roll out continuous coverage with no gaps, ripples or overlaps that cause slips and trips; create custom-sized floor runners, even around corners
- Proprietary adhesive sticks to the floor with a super-tight grip, but peels up easily to replace when mat shows signs of wear
- Sticks to most commercial floor surfaces including concrete, VCT, linoleum, ceramic tile, quarry tile and laminate flooring
- Easy to clean: you can sweep, vacuum, mop, use your shop/wet vac or run your floor scrubber and it won't budge
- The thinnest commercial floor mat you can buy: no rippled edges to obstruct doors or create tripping hazards; ADA compliant for wheelchairs and walkers; carts and pallet jacks roll right over it
- Stays in place for up to 3 months, depending on conditions and traffic patterns
- Absorbs a wide variety of liquids including water, oil and grease; leakproof backing prevents liquid from soaking through to the floor



- Tested and Certified by the National Floor Safety Institute (NFSI): when used as part of your floor safety program, high-traction surfaces such as PIG Grippy Floor Mat have been proven to reduce slip-and-fall claims by as much as 90%



Item#	Description	Dimensions	Weight
GRPSB36200-BK	Black	36" W x 100' L	25.52 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
GRPSB36200-BK	Black	91.4cm W x 30m L	11.6 kg

Specifications

Traffic	Heavy Foot Traffic; Carts & Equipment
Backing Material	Adhesive-Backed
Indoor/Outdoor	Indoor Use
Incinerable	Yes
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Water; Grease; Oils
Dimensions	36" W x 100' L
Mat Weight	Mediumweight
Absorbency	Up to 8 gal. per roll
Brand	PIG
Core Diameter	3"
Industry	Industrial Facilities; Manufacturing; Shops & Garages
Perforated	No
Storage Temp Range	Store between 32°F and 120°F
Temperature Limit	Surface temps from 55°F to 120°F
Walking Surface	Absorbent Top
Sold as	1 roll
Weight	25.52 lbs.
# per Pallet	18
Composition	Absorbent - Polypropylene Adhesive Backing - Proprietary Adhesive Material
UNSPSC	47131901

UV Resistant

No

Pigalog® Page Number

Page 232

Metric Equivalent

Absorbency

Up to 30.3 L per roll

Dimensions

91.4cm W x 30m L

Weight

11.6 kg

Technical Information

Certifications, Approvals and Ratings

ADA Compliant,NFSI Certified,ANSI B101.1- 2009

Technical Documents

[PIG Adhesive-Backed Mats](#)

[New Pig Adhesive-Backed Mat Notice](#)

[PIG® Grippy® Floor Mats](#)

[29 CFR 1910.22\(a\)\(2\)](#)

Disclaimers

[Safety Instructions Regarding Flammable Liquids for Flame Resistant Mats](#)

Pig Absorbent Mats are flame resistant in their unused state, but take on the properties of flammable liquids they absorb. Always take proper precautions against potential ignition in handling and disposal of these mats if they have absorbed flammable liquids. For further assistance, please call Technical Services.

[Color Variation Statement](#)

It is normal for top layer materials to show minor variations in color between production runs. This is particularly true for the grades of materials used in consumable or disposable products such as our adhesive-backed mats. New Pig makes every effort to achieve consistent color, but some variance is possible. Perceived differences in color may also result from mat layout orientation or uneven traffic wear patterns.



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com