

# SCALE MASTER® PRO XE

ADVANCED DIGITAL PLAN MEASURE

Dual LCD displays and improved ergonomic design makes it easier for left- or right-handed use. Optional PC interface lets you transfer measurements quickly and accurately to spreadsheets and estimating programs.

## Easy to Learn, Easy to Use

- Complete takeoffs from blueprints and plans with speed and accuracy
- Reduce errors on estimates and bids
- Optional PC interface
- 91 Built-in scales support U.S. and Metric
- 10 Custom scales for out-of-scale drawings

## Ideal For:

Architects,  
Builders, Contractors,  
Engineers, Estimators  
(Concrete, Electrical,  
Excavating, Fencing,  
HVAC, Paving,  
Plumbing)

 **CALCULATED  
INDUSTRIES®**

**FAST. ACCURATE. RELIABLE.**

4840 Hytech Drive  
Carson City, NV 89706  
1-800-854-8075  
www.calculated.com

The **SCALE MASTER® PRO XE** makes it easy to do Linear, Area and Volume takeoffs with speed, accuracy and confidence when estimating, bidding or planning. The ergonomic design makes it comfortable to hold, and the dual LCD displays make it much easier to read. **SCALE MASTER® PRO XE** provides transfer capabilities from plans, blueprints and maps as well as out-of-scale drawings.

## FEATURES

### Dimensional Math and Conversions:

- Wide range of dimensional units: Use best-suited units to fit your work — Decimal Inches, Feet-Inches, Decimal Feet, Yards, Miles, Nautical Miles, Millimeters, Centimeters, Meters, Kilometers — including Square and Cubic formats.
- 91 built-in scales: 50 U.S. (Feet-Inch) and 41 Metric for maximum versatility in architectural, engineering and civil/map scaling.
- Ten custom scales: Five each for U.S. and Metric units, lets you “roll” or define any scale, even from plans that have been reduced, enlarged or are out of scale. Permanently store the new scale for future use.

### Dedicated Functions:

- Dedicated Length, Width and Height keys: Roll, store and recall L, W & H values and instantly find rectangular Areas and Volumes.
- Auto Count feature: Automatically counts how many times a pre-set distance has been rolled. Great for stud counts, columns, fence posts, outlets, fixtures or any other regularly spaced items.
- Count while rolling: Push-button counter lets you manually count items as needed while you roll.
- Constant (+K) Key: Allows you to add (or subtract) a constant value to the distance measured. Great for take-outs and add-ons.

### Time-Saving Utilities:

- Lock Switch: Lock in the mode, scale and units to prevent changing them while rolling.
- Subtract Key: Allows you to easily deduct rolled distances.
- Accumulating (M+) Memory: Allows easy totaling of dimensions or counts — perfect for multi-page plans.
- PC ready: The PC interface lets you transfer any rolled values from the **SCALE MASTER® PRO XE** directly to commonly used spreadsheets or estimating programs. USB cable sold separately.
- Auto Shut-off

## INCLUDES

- Hard Cover Protective Case
- User's Guide
- Two CR2032 Long-life Lithium Batteries
- One-Year Warranty



Model  
6135

# Now you can easily finish complete takeoffs, quickly and accurately.

Easily switch between U.S. and Metric scales.

Easy-to-read displays for left- or right-handed use.

Length, Width and Height functions let you roll, store and recall values. Instantly find rectangular Areas and Volumes, Wall Areas and Perimeters.

Add (or subtract) a constant value to the distance measured. Great for take-outs and add-ons.

Subtract from the last measured distance. Great for take-outs.

Precision wheel allows rolling in either direction and with either hand.

91 built-in scales help you measure plans, blueprints and maps. Ten Custom scales for out-of-scale drawings.

Select dimensional units for maximum versatility: Decimal Inches, Feet-Inches, Decimal Feet, Yards, Miles, Nautical Miles, Millimeters, Centimeters, Meters, Kilometers — including Square and Cubic formats.

Add and subtract with the built-in accumulative Memory.

Built-in Counter lets you manually or automatically count other items — studs, pliers, outlets, etc.

Transfer values to spreadsheets and estimating programs. Optional PC interface cable required.

Pointer shows you the exact start point and stop point.



## SPECIFICATIONS

**Size:** 7.3 x 1.9 x 0.6" (185 x 48 x 15mm)

**Product Weight (including batteries):** 2.1 oz. (60g)

**Power:** Two 3-volt lithium (CR2032) batteries (included)

**Display Type:** LCD segment; 7-digit main display, 3-digit count, 5-digit scale display, with annunciator legends

**Wheel Resolution:** 0.025" (0.635mm)

**Accuracy:** 2-4%, based on user's start & stop accuracy; 12-digit internal accuracy

**PC Interface:** Requires optional 15' USB interface cable; works with Windows® operating systems



## OPTIONAL PC INTERFACE CABLE FOR THE SCALE MASTER® PRO XE

Part #5006

(15 feet • 4.6 meters)

Instantly send values directly from your Scale Master Pro XE to your favorite PC spreadsheet or estimating program.

### System Requirements:

- Windows® compatible computer and USB port
- No additional software or drivers needed!*

Scale Master Pro XE Combo Kit (Model #6335) includes the PC Interface Cable.