



# R-068

Cut resistant fully coated impact glove



Impact

Abrasion Protection



Cut

Liquid Spray & Splash



Oil



Light Duty

## Innovative impact, cut, and liquid protection combined with superior dexterity for ultimate comfort in a variety of end uses

- The Ringers 068 R-Flex Impact glove with Nitrile Full Dip combines protection against impact hazards with full-dipped coverage for liquid protection and the highest levels of cut resistance when you need it most.
- Developed with Ringers' F3 Technology™ and patented TPR design for superior dexterity and comfort.
- An additional half-dipped sandy finish palm ensures secure grip in wet and dry environments, and touchscreen compatible index, middle and thumb tips allow technology interaction.



### Industries

- Construction
- Oil and gas
- Manufacturing
- Mining
- Automotive Aftermarket
- Chemical
- Emergency Medical Services
- Machinery and Equipment
- Metal fabrication

### Applications

- Running tools into the wellbore
- Assembly and disassembly of large pipes
- Engagement and release of drill string slips
- Unloading and stacking pipe
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Loading and hauling
- Assembling and mounting components
- Concentration mixing and palletisation
- Hydraulic repair
- Use of binding agents
- Smelting and cleaning of equipment
- Re-fuel oil fluid and diesel
- Tank Cleaning

[WWW.ANSELL.COM](http://WWW.ANSELL.COM)

**Ansell**



# R-068

Cut resistant fully coated impact glove

## Key Features

- TPR impact protection on top of hand and full length of fingers
- Patented double dipped technology
- Full-dipped nitrile in smooth finish for liquid resistance
- Half-dipped nitrile coating on palm with sandy finish for enhanced grip
- Sandy finish for superior grip on wet and dry surfaces
- High visibility for increased safety
- Touchscreen compatible index, middle and thumb tips

## Performance Standards & Regulatory Compliance

### REACH Compliant



## Specifications

| BRAND   STYLE | DESCRIPTION   | Gauge | SIZE                 | COLOR  | PACKAGE                       |
|---------------|---|-------|----------------------|--------|-------------------------------|
| RINGERS R068  | <b>Finishing:</b> Fully Dipped<br><b>Coating Material:</b> Nitrile<br><b>Liner Material:</b> HPPE<br><b>Cuff Style:</b> Knitwrist | 13    | 8, 9, 10, 11, 12, 13 | Hi Viz | • 10 pairs/bag, 6 bags/carton |

## For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

