



Never before have goggles offered such comfort and protection as well as sleek, futuristic styling. The Uvex Stealth goggle combines modern design, technology, materials and high-performance lens coatings to create the highest levels of worker comfort and acceptance. One of the most popular goggles on the market, the Uvex Stealth makes it easy — even fashionable — to wear goggles on the job.



SAFETY GOGGLES

Uvex Stealth®



UVEX™
by SPERIAN

Uvex Stealth®

Exceptional Performance


- Low profile design and indirect venting system for chemical splash and impact protection.
- Frame and lens are impact resistant and provide greater than 99.9% protection from harmful UV rays.
- Uvextreme® anti-fog coating and indirect ventilation system minimize fogging.
- Dura-streme™ technology option delivers Uvextreme anti-fog protection on the interior of the lens and Ultra-dura® hard coat on the exterior of the lens for greater chemical and scratch resistance and up to 3x* longer lens life.
- Available in Clear, Amber and Gray lens tints for a variety of applications.
- Meets ANSI Z87.1-2003 (High Impact) and CSA Z94.3 standards.

Superior Comfort & Fit

- Toric lens provides superior optics and unobstructed peripheral vision.
- Soft, elastomer body flexes and conforms to the face for a secure, comfortable, gap-free fit.
- Pivoting, quick-adjust headband provides easy adjustment for a comfortable fit.

Product Platform Advantages & Value


- One of the easiest and most cost effective lens replacement systems on the market.
- Lens replacement system allows for multiple lens tints and extends the life of the goggle.
- Dura-streme coating extends the life of the lens.
- Rx insert provides flexibility for workers who require vision correction.




Indirect ventilation system channels air flow over lens. This minimizes fogging and improves vision while still providing superior splash and impact protection.



Quick-adjust headband clips permit fast and easy fitting, even on hardhats. Once adjusted correctly the textured headband won't slip.



Soft, flexible elastomer seal stays amazingly soft, pliable and comfortable for the life of the frame. The result is a superior fit around the nose, cheeks and forehead.



Specially designed Rx carrier provides unique protection to workers requiring prescription eyewear.



*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

Uvex Stealth®



Clear — Ideal for most indoor work applications



Amber — Ideal for low-light applications where enhanced contrast is needed



Gray — Minimizes outdoor sunlight and glare



All Uvex® lenses offer 99.9% ultra-violet protection.

ORDERING INFORMATION

GOGGLES

ITEM #	BODY COLOR	LENS TINT	LENS COATING	HEADBAND	UPC CODE
S39630C	Orange/Gray	Clear	Uvextreme®	Neoprene Band	603390121682
S39630CI	Orange/Gray	Clear	Uvextreme	Fabric Headband	603390121692
S39631C	Orange/Gray	Gray	Uvextreme	Neoprene Band	603390121708
S3960C	Gray/Gray	Clear	Uvextreme	Neoprene Band	603390035883
S3960D	Gray/Gray	Clear	Dura-streme™	Neoprene Band	603390122873
S3960CI	Gray/Gray	Clear	Uvextreme	Fabric Headband	603390039331
S3961C	Gray/Gray	Gray	Uvextreme	Neoprene Band	603390035890
S3962C	Gray/Gray	Amber	Uvextreme	Neoprene Band	603390035937
S39610C	Teal/Gray	Clear	Uvextreme	Neoprene Band	603390035906
S39611C	Teal/Gray	Gray	Uvextreme	Neoprene Band	603390035913

REPLACEMENT LENSES

ITEM #	LENS TINT	LENS COATING	UPC CODE
S700C	Clear Repl. Lens	Uvextreme	603390035975
S700D	Clear Repl. Lens	Dura-streme	603390122903
S701C	Gray Repl. Lens	Uvextreme	603390035982
S702C	Amber Repl. Lens	Uvextreme	603390035999

ACCESSORIES

ITEM #	DESCRIPTION	UPC CODE
S3959	Rx Carrier	603390039997
S8999	Rx Pattern	603390043093
S821	Gray Neoprene Band w/out Slides	603390038150
S823	Gray Flame Retardant Fabric Band	603390025464

FOR MORE INFORMATION, CONTACT:

Sperian Protection Americas, Inc.
 900 Douglas Pike
 Smithfield, RI 02917-1874
 (800) 430-5490
www.uvex.us

Packaging information
 (Goggles)

Ind. Box, 50/master case
 Master Case Weight: 15 pounds
 Master Case Dimensions: 20" x 19" x 17"

(Replacement Lenses)
 Ind. Polybag, 10/stocker

(Accessories)
 Rx Carrier: 10/stocker
 Rx Pattern: Individual
 Headbands: 25/bag



Uvextreme® anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura® hard coat is permanently bonded to the lens and is scratch-resistant and chemical-resistant. Uvex Dura-streme™ lenses combine our two best lens coatings on one lens: Ultra-dura on the exterior and Uvextreme on the interior to provide up to 3x* more lens life.

*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

