

SHOWA

7714R

With a cotton-lined PVC construction and rough grip combined with a 14" gauntlet, SHOWA 7714R provides defensive protection from chemicals, oils and grease, perfect for any and all general-purpose industrial applications.

FEATURES

- PVC coated
- Cotton jersey liner
- 14" gauntlet
- Rough grip

BENEFITS

- One of the most durable work gloves available
- Provides workers barrier protection from chemicals, oil and grease
- Provides abrasion resistance
- Versatile and durable

INDUSTRY



Chemical



Engineering



Janitorial



Municipal Services

IDEAL APPLICATIONS

- Chemical spray and treatment
- Coating preparation
- Laboratory, pharma & analysis
- Painting & spray workshops
- Assembly dry and oily parts
- Maintenance
- Washing & cleaning
- Public utility



TAA PRODUCTS

MATERIAL

- Cotton
- Cotton jersey
- Cut and sewn

COATING

- chemical resistant
- PVC
- Water resistant

GRIP

- Rough

STANDARDS



Cat. III

2777

EN ISO 374-1:2016/Type B



AKL

EN 388:2016



3111X

EN ISO 374-5:2016



SHOWA
7714R



PACKAGING

- 12 Pair per polybag
- 6 Polybags per case
- 72 Pair per case



COLOUR

- Black



SIZES

- L



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
7712R



MATERIAL
Cotton
COATING
chemical resistant

SHOWA
7710R



MATERIAL
Cotton
COATING
chemical resistant

SHOWA
7712R



MATERIAL
Cotton
COATING
chemical resistant

SHOWA
6781R



MATERIAL
Cotton
COATING
chemical resistant

[USER INSTRUCTIONS

Protection against mechanical risks, with electrostatic properties. Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. All clothing and shoes worn with the glove with electrostatic dissipation properties must also be designed taking the electrostatic risk into account.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved