



EAN:	4013288113900	Size:	260x205x55 mm
Part number:	05030170001	Weight:	408 g
Article number:	1578 A/6	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Micro screwdriver set for slotted and cross-recess screws, Phillips
- ESD-safe tool thanks to surface resistance of $< 10^9 \text{ Ohm}$
- Multi-component Kraftform Micro handles for fast and ergonomic screwdriving
- Hexagonal anti-roll feature against rolling away
- The Wera Black Point tip offers an exact fit and optimum corrosion protection

ESD-safe Wera Micro screwdriver set. Dependable protection against electrostatic energy and associated damage. Rapid twisting results from fixing the hand on the head and using the fast-turning zone just below. This makes time-consuming grip adjustments unnecessary. Power zones with integrated soft sections ensure the transfer of high loosening and tightening torque; a precision zone for the right rotation angle during fine adjustment work. The Black Point tip offers optimised corrosion protection and an exact fit.

Web link
https://products.wera.de/en/screwdrivers_esd_series_1578_a_6.html

Wera - 1578 A/6
 05030170001 - 4013288113900

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

ESD Series

Set contents:



1550 PH ESD Micro

05030111001¹⁾ 1 x PH 0 x 60 mm

05030112001 1 x PH 1 x 80 mm

1) Size 0 modified according to JCIS 0 (Japanese Camera Industrial Standard)



1578 A ESD Micro

05030100001 1 x 0.25 x 1.2 x 40 mm

05030101001 1 x 0.23 x 1.5 x 40 mm

05030102001 1 x 0.30 x 1.8 x 60 mm

05030104001 1 x 0.40 x 2.5 x 80 mm



Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

High protection




The electric surface resistance of the Wera ESD material is $\leq 10^9$ ohm. This securely protects components against electrostatic energy and associated damage.

Kraftform Micro Handle



Multi-component screwdriver handle for ergonomic working.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

Web link

https://products.wera.de/en/screwdrivers_esd_series_1578_a_6.html

Wera - 1578 A/6

05030170001 - 4013288113900

Wera Werkzeuge GmbH

Korzter Straße 21-25


D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de


ESD Series

The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allow rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

“Take it easy” Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/screwdrivers_esd_series_1578_a_6.html

Wera - 1578 A/6
05030170001 - 4013288113900

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de