


PIG® Carpet Protection Berber Runner with Adhesive Backing

GRPCP916X10 FOR USE ON CARPETED SURFACES ONLY, 6' x 10', 1 roll

It's the adhesive-backed mat made just for carpet! Protect your carpeted surfaces from dirt, stains and wear in high traffic areas.

- Non-slip 6' x 10' Berber runner sticks to carpet and traps dirt, salt, water, grease and grime to prevent it from damaging carpet fibers
- Adhesive backing keeps the runner in place on low pile, commercial carpeted surfaces; will not shift, flip, bunch up or get caught in opening or closing doors
- Covers up carpet that's excessively worn, stained or damaged from excessive traffic patterns; reduces the need for total carpet replacement or professional cleaning
- Protects new carpet and extends the life of existing carpet; stops premature crushing and wear
- Polyester blend is soft and pliable (polyester content is 100% post-consumer recycled)
- Cuts easily so you can create the size you need to fit your application
- ADA-compliant and low profile; eliminates trip hazards caused by traditional rubber-backed floor mats
- Easy to maintain — vacuum daily or deep clean with a carpet extractor
- Ideal for doorways between manufacturing and office spaces, long hallways and transition areas, building entrances, customer service counters, coffee stations and other high traffic or standing carpeted areas
- For use indoors on carpeted surfaces only
- All adhesives have the potential to leave a residue. For best practice when changing out the runner, clean the carpet with a carpet extractor to remove any tackiness that may be left behind before installing a new runner



Item#	Description	Dimensions	Weight
GRPCP916X10-BK		6' W x 10' L	12 lbs.

GRPCP916X10-GY

6' W x 10' L

12 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
GRPCP916X10-BK		182.9cm W x 3m L	5.4 kg
GRPCP916X10-GY		182.9cm W x 3m L	5.4 kg

Specifications

Dimensions	6' W x 10' L
Mat Weight	Heavyweight
Recycled Content	100% Post-Consumer Recycled Polyester Fabric
Absorbency	Up to 5.4 gal. per roll
Brand	PIG
Category	Carpet Protection Mat
Flammability Specifications	Flame Resistant - Will melt and self-extinguish
Fluid Absorbed	Water; Grease; Oils
Incinerable	Yes
Industry	Commercial Facilities/Retail
Intended Use	FOR USE ON CARPETED SURFACES ONLY
Special Feature	For Use on Carpet
Storage Temp Range	Store between 32°F and 120°F
Temperature Limit	Surface temps from 55°F to 120°F
Traffic	Heavy Foot Traffic; Carts & Equipment
UV Resistant	Yes
Sold as	1 roll
Weight	12 lbs.
# per Pallet	48
Composition	Absorbent - Polyester Adhesive Backing - Proprietary Adhesive Material
UNSPSC	47131901
Pigalog® Page Number	Page 223

Metric Equivalent

Absorbency	Up to 20.4 L per roll
Dimensions	182.9cm W x 3m L
Weight	5.4 kg

Technical Information**Certifications, Approvals and Ratings**

ADA Compliant

Technical Documents

[PIG Carpet Protection Berber Runner with Adhesive Backing](#)

[New Pig Adhesive-Backed Mat Notice](#)

[FAQ for PIG Carpet Protection Runner with Adhesive Backing](#)

[Instructions for PIG Carpet Protection Runner with Adhesive Backing](#)

[PIG® Carpet Protection Berber Runner Mat with Adhesive Backing](#)

[29 CFR 1910.22\(a\)\(2\)](#)



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com