



**MCR
SAFETY**

Rattler Goggles Series

Specification Sheet

PRODUCT DESCRIPTION:

Rattler™ features interchangeable 3-position ratcheting bayonet temples and an adjustable head band with each pair. A unique feature of the head band with hook and loop closure is the ability to adjust with one hand while wearing. The Rattler™ also features full length, non-slip TPR temple sleeves for comfort and grip. A closed cell foam seal provides optimum protection from small particles and debris. The light weight nylon frame and polycarbonate wrap-around lens design provides greater side impact protection. Anti-fog lens offerings include clear, gray, amber, and indoor/outdoor clear mirror in both black and silver frames and are treated with our exclusive Duramass® scratch-resistant coating.



FEATURES:

- Interchangeable 3-position ratcheting bayonet temples & an adjustable head band with each pair
- Closed cell foam seal provides optimum protection from small particles and debris
- Rugged polycarbonate lens filters 99.9% U.V. rays
- Light weight nylon frame

TECHNICAL DATA FOR: RT110AF

Series	Rattler	Scratch Resistant	Yes
Category	Goggles	Frame Material	Nylon
Dielectric	Yes	Packaging	Multicolor Gravity Feed
Anti-Fog	Anti-Fog	Goggle Type	Indirect Vented
Case Pack	144 pair	AS/NZS 1337.1	Yes
Case Dimensions	20.472 x 19.291 x 12.992	CE EN166	Yes
Case Weight	26.721 oz.	ANSI D3 SPLASH	N/A
Made In	Taiwan	ANSI D4 DUST	N/A
MIL - PRF - 31013	N/A	CAN/CSA Z94.3	Yes
ANSI Z87+	Yes		

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Goggle Type:
----------	---------------	---------------	--------------------	-------	--------------	--------------

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

Rattler Goggles Series Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Goggle Type:
RT110AF	Clear	Duramass Anti-Fog	Yes	90	Black	Indirect Vented
RT112AF	Gray	Duramass Anti-Fog	Yes	13	Black	Indirect Vented
RT114AF	Amber	Duramass Anti-Fog	Yes	80	Black	Indirect Vented
RT120AF	Clear	Duramass Anti-Fog	Yes	90	Silver	Indirect Vented
RT122AF	Gray	Duramass Anti-Fog	Yes	13	Silver	Indirect Vented
RT129AF	I/O Clear Mirror	Duramass Anti-Fog	Yes	36	Silver	Indirect Vented
RTH10AF	Clear	Duramass Anti-Fog	Yes	90	Black	Indirect Vented
RTH15AF	Clear	Duramass Anti-Fog	Yes	90	Black	Indirect Vented
RTH20AF	Clear	Duramass Anti-Fog	Yes	90	Black	Indirect Vented
RTH25AF	Clear	Duramass Anti-Fog	Yes	90	Black	Indirect Vented

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved