

SHOWA

6781R

Constructed with a triple-layered foam insulation and a strong neoprene coating, the SHOWA 6781R protects you from heat and cold.

FEATURES

- Fully neoprene-coated cotton jersey
- Triple layered foam insulation
- 12" Gauntlet
- Rough finish

BENEFITS

- Insulation against intermittent heat up to 500°F or cold
- Neoprene coating provides outstanding resistance to abrasion, cut and a wide range of chemicals

INDUSTRY



Automotive



Chemical



Metallurgy



Oil and Gas

IDEAL APPLICATIONS

- Chemical spray and treatment
- Coating preparation



TAA PRODUCTS

MADE IN USA

MATERIAL

- Cotton

COATING

- chemical resistant
- Neoprene
- Water resistant

GRIP

- Rough

STANDARDS



EN ISO 374-1:2016/Type A



AJKLMT
EN 407



EN ISO 374-5:2016



EN 511



SHOWA
6781R



- PACKAGING**
- 12 Pair Per Carton
 - 6 Cartons Per Case
 - 72 Pair per case

- COLOUR**
- Black

- SIZES**
- L



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
6780-20



MATERIAL
Cotton

COATING
chemical resistant

SHOWA
6780R



MATERIAL
Cotton

COATING
chemical resistant

SHOWA
6784



MATERIAL
Cotton

COATING
chemical resistant

SHOWA
6781R-06



MATERIAL
Cotton

COATING
chemical resistant

[USER INSTRUCTIONS

Protection against mechanical risks, with electrostatic properties. Do not use where there are chemical, electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. All clothing and shoes worn with the glove with electrostatic dissipation properties must also be designed taking the electrostatic risk into account. Do not use where there are chemical, electrical or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. Store in a dry place, away from the light. Gloves must not come in contact with an open flame.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAGroup.com

© SHOWA Group 2018 | All rights reserved